

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION  
CAST IRON CONSTRUCTION

ENCLOSURE: TOTALLY ENCLOSED  
MOUNTING: FOOT

FRAMES 404TSC-405TSC

COOLING: FAN COOLED



617437-221

D

C

B

A



D

C

B

A

MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END  
OF SHAFT EXTENSION IS .002 T.I.R.

WEIGHT (LBS): 1326  
MOTOR WEIGHTS MAY VARY BY 15% DEPENDING UPON RATING.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: CHG AH FROM 4.29 TO 4.00			
REV: A	VERSION: 01	REVISED: 02:28:01 02/14/2025	TDR: 000001250549
MODEL NO. 617437-221			REF: -
BY: RAGGDM			<b>B</b>

BALDOR - RELIANCE

405/4TSC TEFC F1 FT CI 2X3"

617437-221