ABB BALDOR RELIANCE

Customer information packet

CEM4115T-G

50HP, 1775RPM, 3PH, 60HZ, 326TC, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/18/2026 8:13:42 AM

Specifications

Enclosure	TEFC
Frame	326TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	NEMA PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	58.000 A @ 460.0 V
	116.000 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	58.0 a

Part Detail

Revision	H
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	12WGY141
Layout	12LYH471
Eff. date	03-02-2026
CD Diagram	CD0180
Poles	04
Leads	9#8
Proprietary	False
Created date	12-16-2019

Insulation Class	H
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1272M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	30.28 IN
Power Factor	85
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.125 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3443LUA											
CAT.NO.	CEM4115T-G			**CUST. P/N**						**ENCL**	TEFC
SPEC.	12-0000-1381	**CC**	010A	**FRAME**	326TC		**SER.NO.**				
HP	50		**CLASS**	H	**HZ**	60					
R.P.M.	1775		**PH.**	3	**DES.**	A					
VOLTS	230/460			**CODE**	H		**ODE BRG**	6311	**DE BRG**	6312	
AMPS	116/58										
RATING	40C AMB-CONT			**NEMA NOM. EFF.**	94.5			**GREASE**	POLYREX EM		
P.F.	85	**SER.F.**	1.15	**CT6-60H(10:1)VT3-60H(20:1**							
USABLE AT	50HZ 50HP 190/380V 139/69.5A			SF1.0							
VOLTS	**AMPS**		**MAX. SPACE HEATER TEMP.**								

AC Induction Motor Performance Data
Record # 35498
Typical performance - not guaranteed values

Winding: 12WGY141-R004	**Type:** 1272M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			50	**Full Load Torque**	147 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			116/58	**Breakdown Torque**	396 LB-FT
R.P.M.			1775	**Pull-up Torque**	183 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	254 LB-FT
NEMA Design Code	A	**KVA Code**	G	**Starting Current**	395 A
Service Factor (S.F.)			1.15	**No-load Current**	19.8 A
NEMA Nom. Eff.	94.5	**Power Factor**	85	**Line-line Res. @ 25ºC**	0.10889 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	64°C
S.F. Amps				**Temp. Rise @ S.F. Load**	79°C
				Locked-rotor Power Factor	26
				Rotor inertia	9.59 lb-ft²

Load Characteristics 460 V, 60 Hz, 50 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	53	74	83	85	87	87	87
Efficiency	91.3	94.3	94.8	94.6	94	93.1	94.2
Speed	1794.5	1789.3	1783.5	1777.5	1770.7	1761.5	1773
Line amperes	24.2	33.5	44.7	57.6	71.5	90	65.9


ABB Motors and Mechanical Inc.


WINDING # 12WGY141

50 HP 3 PH 60 HZ 1775 RPM 460 V 1272M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=396 PU=183 LR=254 LRA=395




12LYH471
(1232-1278) = 30.50
14.00
5.00
.25
GREASE FITTING & GREASE TUBE
GREASER & RELIEF (EA. END)
.50 KEY 3.88 LONG
Ø 13.40
Ø 12.500 12.497
Ø 2.125 2.124
SLINGER
GREASE RELIEF W/ GREASE TUBE
8 HOLES Ø .66
10.50
10.50
12.00
14.00
1.00
5.25
DRAIN FITTING (EA. END)
17.64
14.67
8.23
45°
45°
3.22
4 HOLES .62-11 TAP 1.00 DEEP Ø 11.00 B.C.
16.23
8.00 +.00 -.06
LEAD HOLE Ø 2.00
6.25
6.25
12.07
7.25
14.50
INTERNAL SHAFT GROUND BP5307
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD DRAWING TO SOLIDWORKS
REV: B
VERSION: 02
REVISED: 01:43:40 06/14/2022
TDR: 000001192277
MODEL NO. 12LYH471
REF: -
BY: ENALEM0
B
BALDOR
HORZ TEFC 324-6TC W/AEGIS INT SH GND
12LYH471

CD0180





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1