

ABB BALDOR RELIANCE III

Customer information packet

CEM7026T-I-5

3HP, 3450RPM, 3PH, 60HZ, 182TC, 3622M, XPFC, F1

Class - CLI GP C,D

Division - Division I

Specifications

Enclosure	XPFC
Frame	182TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UL CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.900 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	2.9 a
Insulation Class	F

Part Detail

Revision	L
Type	AC
Mech. spec.	36P268
Base	
Status	PRD/A
Elec. spec.	36WGS504
Layout	36LYP268
Eff. date	04-16-2024
CD Diagram	CD0006
Poles	02
Leads	3#16
Proprietary	False
Created date	12-03-2013

Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3622M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	18.09 IN
Power Factor	91
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0977XPSL												
NO.							CC	010A				
SER.							TEMP CODE			T3C		
SPEC.	36P268S504G1											
CAT.NO.	CEM7026T-I-5											
HP	3											
VOLTS	575											
AMPS	2.9											
RPM	3450				MOTOR WEIGHT				80			
HERTZ	60	PH	3	CL	F	DE BRG	6206					
SER.F.	1.15	DES	B	CODE		K	ODE BRG			6205		
FRAME	182TC		GREASE		POLYREX EM							
RATING	40C AMB-CONT 55C AMB @ 1.0 SF											
					NEMA-NOM-EFF				86.5		PF	91
	NEMA MG-1 PT 5,IP55											

AC Induction Motor Performance Data

Record # 50287

Typical performance - not guaranteed values

Winding: 36WGS504-R004			Type: 3622M	Enclosure: XPFC	
Nameplate Data			575 V, 60 Hz: Single Voltage Motor		
Rated Output (HP)		3	Full Load Torque		4.71 LB-FT
Volts		575	Start Configuration		direct on line
Full Load Amps		2.9	Breakdown Torque		19.7 LB-FT
R.P.M.		3450	Pull-up Torque		12 LB-FT
Hz	60	Phase	Locked-rotor Torque		14.1 LB-FT
NEMA Design Code	B	KVA Code	Starting Current		26.6 A
Service Factor (S.F.)		1.15	No-load Current		0.936 A
NEMA Nom. Eff.	86.5	Power Factor	Line-line Res. @ 25°C		7.26 Ω
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		52°C
S.F. Amps			Temp. Rise @ S.F. Load		64°C
			Locked-rotor Power Factor		48.2
			Rotor inertia		0.0984 LB-FT2

Load Characteristics 575 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	66	82	88	91	92	93	92
Efficiency	80.4	86	87.4	87	86	84.4	86.4
Speed	3565	3535	3504	3472	3434	3393	3449
Line amperes	1.25	1.74	2.35	2.94	3.66	4.4	3.37


ABB Motors and Mechanical Inc.

WINDING # 36WGS504

Typical performance - not guaranteed values.

3 HP 3 PH 60 HZ 3450 RPM 575 V 3622M

TORQUES (LB-FT): PO=19.7 PU=12 LR=14.1 LRA=26.6



CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10: 24: 49 02/19/2019

BY: ENBRIRO

MTL: —


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1