ABB BALDOR RELIANCE

Customer information packet

CEM4314T-G

60HP, 1780RPM, 3PH, 60HZ, 364TC, A3658M, TEFC
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 12:47:31 AM

Specifications

Enclosure	TEFC
Frame	364TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	60.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	140.000 A @ 230.0 V
	152.000 A @ 208.0 V
	70.000 A @ 460.0 V
Design Code	B
Duty Rating	CONT
Efficiency @ 100% Load	95.0 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	70.0 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A3658M

Part Detail

Revision	C
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG4075
Layout	617428-019
Eff. date	02-13-2025
CD Diagram	416820-002
Poles	04
Leads	3#4,6#6
Proprietary	False
Created date	08-24-2021

Mounting Arrangement	F1
Number of Poles	4
Overall Length	33.43 IN
Power Factor	84
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Service Factor	1.15
Shaft Diameter	2.374 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1780 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP3979LUA

CAT #	CEM4314T-G			**SER**				**CC**	010A											
SPEC	A36-7861-4075			**RATING**	40C AMB-CONT															
HZ	**VOLTS**			**AMPS**			**RPM**	**HP**	**CODE**		**SF**	**DES**		**PF**		**NEMA NOM. EFF**				
60	230/460			140/70			1780	60	G		1.15	B		84	%	95	%			
	-														%		%			
PH	3	**CL**	H	**MAX CORR KVAR**	15															
BRG	**DE**	6313		**ODE**	6313		**ENCL**	TEFC		**FR**	364TC									
GREASE	POLYREX EM									**MTR WT**	907	**LBS**								
USABLE AT	50HZ 50HP 190/380V 138/69A									SF1.0										
INVERTER DUTY	**CT**	15-60	**HZ**	4:1	**VT**	3-60	**HZ**	20:1	**CHP**	60-90	**HZ**	1.5:1	**1.0 SF VPWM**							
MAX RPM	2700																			

617428-019


DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION
CAST IRON CONSTRUCTION

ENCLOSURE: TOTALLY ENCLOSED
MOUNTING: FOOT

FRAMES 364TC-365TC

COOLING: FAN COOLED



MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STD. SHAFT EXTENSION IS .002 T.I.R. UP TO AND INCLUDING 1.625 DIA AND .003 T.I.R. 1.625 DIA. TO 5 INCH DIA.

WEIGHT (LBS): 364TC = 815
365TC = 855

MOTOR WEIGHTS MAY VARY BY 15% DEPENDING UPON RATING.

CENTER OF GRAVITY WITH X & Y VARY ± 1.0 INCH FROM CENTER.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: FIX COG			
REV: D	VERSION: 04	REVISED: 09:34:56 05/28/2019	TDR: 000001109340
MODEL NO. 617428-019			REF:
BY: RAGJSS1			B


BALDOR


DIM SHEET 364-5TC TEFC (611740-003-SH1)

617428-019

416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED





(N. P. 1575-B)

REV. DESC: ADJUST TEXT DARKNESS		
REV. LTR: B	VERSION: 02	TDR: 000001285318
FILE: \RAG\00022\453	REVISED: 09:36:26 09/24/2026	BY: USJOSUL
MTL: –		

ABB

CONN DIAG – STANDARD 9 LEAD, DELTA-CONNECTED

SH1 of 1

416820-002