ABB BALDOR RELIANCE

Customer information packet

CEM7014T-I

1//.75HP, 1760//1460RPM, 3PH, 60//50HZ, 143T
Class - CLI GP C,D
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 12:15:42 AM

Specifications

Enclosure	XPFC
Frame	143TC
Frame Material	Steel
Frequency	50.00 Hz
	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 50 HZ
	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	380.0 V @ 50 HZ
	230.0 V @ 60 HZ
	190.0 V @ 50 HZ
Agency Approvals	CSA EEV
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.260 A @ 230.0 V
	3.200 A @ 208.0 V
	3.080 A @ 190.0 V
	1.630 A @ 460.0 V
	1.540 A @ 380.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT

Part Detail

Revision	B
Type	AC
Mech. spec.	35X732
Base	
Status	PRD/A
Elec. spec.	35WGG004
Layout	35LYX732
Eff. date	02-21-2024
CD Diagram	CD0005
Poles	04
Leads	9#18 Y
Proprietary	False
Created date	01-10-2022

Efficiency @ 100% Load	85.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	1.5 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X3520M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.36 IN
Power Factor	67
Product Family	Hazardous Location Motor
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1475 rpm
	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line

Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0977XPSLEV											
NO.						**CC**	010A				
SER.						**TEMP CODE**	T3C				
SPEC.	35X732G004G1										
CAT.NO.											
HP	1//.75										
VOLTS	230/460//190/380										
AMPS	3.26/1.63//3.08/1.54										
RPM	1760//1475				**MOTOR WEIGHT**						
HERTZ	60//50	**PH**	3	**CL**	F	**DE BRG**	6205				
SER.F.	1.15	**DES**	B	**CODE**	N	**ODE BRG**	6203				
FRAME	143TC	**GREASE**	POLYREX EM								
RATING	40C AMB-CONT										
				NEMA-NOM-EFF		85.5	**PF**	67			
	SFA 3.46/1.73										

AC Induction Motor Performance Data
Record # 86929
Typical performance - not guaranteed values

Winding: 35WGG004-R009	**Type:** 3520M	**Enclosure:** XPFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1//.75	**Full Load Torque**	2.97 LB-FT
Volts			230/460//190/380	**Start Configuration**	direct on line
Full Load Amps			3.26/1.63//3.08/1.54	**Breakdown Torque**	13.68 LB-FT
R.P.M.			1760//1475	**Pull-up Torque**	7.85 LB-FT
Hz	60//50	**Phase**	3	**Locked-rotor Torque**	9.01 LB-FT
NEMA Design Code	B	**KVA Code**	N	**Starting Current**	14.13 A
Service Factor (S.F.)			1.15	**No-load Current**	1.08 A
NEMA Nom. Eff.	85.5	**Power Factor**	67	**Line-line Res. @ 25ºC**	16.9 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	24°C
S.F. Amps				**Temp. Rise @ S.F. Load**	27°C
				Locked-rotor Power Factor	61.5
				Rotor inertia	0.144 lb-ft²

Load Characteristics 460 V, 60 Hz, 1 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	30	47	60	69	76	79	73
Efficiency	72.1	81.7	84.7	85.7	85.5	84.7	85.6
Speed	1791	1784	1776	1768	1759	1750	1763
Line amperes	1.11	1.22	1.38	1.59	1.82	2.09	1.73


ABB Motors and Mechanical Inc.

WINDING # 35WGG004

1 HP 3 PH 60 HZ 1768 RPM 460 V 3520M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=13.68 PU=7.85 LR=9.01 LRA=14.13



11/19/2026 ACPERF, record # 86929

AC Induction Motor Performance Data
Record # 86930
Typical performance - not guaranteed values

Winding: 35WGG004-R009	**Type:** 3520M	**Enclosure:** XPFC

Nameplate Data				**380 V, 50 Hz: High Voltage Connection**	
Rated Output (HP)			1//.75	**Full Load Torque**	2.68 LB-FT
Volts			230/460//190/380	**Start Configuration**	direct on line
Full Load Amps			3.26/1.63//3.08/1.54	**Breakdown Torque**	12.31 LB-FT
R.P.M.			1760//1475	**Pull-up Torque**	7.45 LB-FT
Hz	60//50	**Phase**	3	**Locked-rotor Torque**	8.55 LB-FT
NEMA Design Code	B	**KVA Code**	N	**Starting Current**	13.12 A
Service Factor (S.F.)			1.15	**No-load Current**	1.06 A
NEMA Nom. Eff.	85.5	**Power Factor**	67	**Line-line Res. @ 25ºC**	16.9 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	22°C
S.F. Amps				**Temp. Rise @ S.F. Load**	25°C
				Locked-rotor Power Factor	67.1
				Rotor inertia	0.144 lb-ft²

Load Characteristics 380 V, 50 Hz, 0.75 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	29	46	58	67	74	79	71
Efficiency	68.3	79	82.7	84	83.7	83.2	83.8
Speed	1492	1486	1479	1471	1463	1455	1466
Line amperes	1.08	1.18	1.32	1.5	1.71	1.95	1.63


ABB Motors and Mechanical Inc.


WINDING # 35WGG004

0.75 HP 3 PH 50 HZ 1471 RPM 380 V 3520M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=12.31 PU=7.45 LR=8.55 LRA=13.12




35LYX732
510-520 = 14.34
521-528 = 15.21
529-535 = 16.09
536-546 = 17.46
4.73
.13
2.12
.13
.19 KEY
1.38 LONG
7.19
X-PROOF NAMEPLATE
FOR HAZARDOUS LOCATIONS
Ø 4.500
4.497
Ø .8750
.8745
6.49
SLINGER
DRAIN FITTINGS
(EACH END)
6 HOLES
.38 DIA.
4.00
2.75
5.00
.50
5.94
6.67
7.18
4 HOLES
.38-16 TAP
.56 DEEP ON
5.88 DIA. B.C.
45°
45°
7.08
3.50
3.44
LEAD HOLE
.75 N.P.T.
2.75
2.75
4.83
3.25
6.50
.0015 MAX
CLEARANCE
.38
.13 MIN.
.006
.004
1.00 MIN.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD TO SOLIDWORKS
REV: B
VERSION: 02
REVISED: 10:56:07 08/30/2019
TDR: 000001117187
MODEL NO. 35LYX732
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
HOR 143-5TC XPFC M,CLI GP C&D,DRILL RIG,ALUM. SLINGER,DRAINS
35LYX732

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS