ABB BALDOR RELIANCE

Customer information packet

CEM7034T

1.5//1HP, 1760//1460RPM, 3PH, 60//50HZ, 145T
Class - CLI GP D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 6:22:49 AM

Specifications

Enclosure	XPFC
Frame	145TC
Frame Material	Steel
Frequency	50.00 Hz
	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 50 HZ
	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	380.0 V @ 50 HZ
	230.0 V @ 60 HZ
	190.0 V @ 50 HZ
Agency Approvals	CSA
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.500 A @ 208.0 V
	4.400 A @ 230.0 V
	3.800 A @ 190.0 V
	2.200 A @ 460.0 V
	1.900 A @ 380.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT

Part Detail

Revision	S
Type	AC
Mech. spec.	35E377
Base	
Status	NLA/A
Elec. spec.	35WGM493
Layout	35LYE377
Eff. date	01-18-2023
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	09-27-2010

Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	1.9 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3526M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	15.23 IN
Power Factor	73
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger

Speed	1460 rpm
	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1426XPSLEV							
NO.		**CC**	010A				
SER.							
SPEC.	35E377M493G1						
CAT.NO.	CEM7034T						
HP	1.5//1	**T. CODE**	T3C				
VOLTS	230/460//190/380						
AMPS	4.4/2.2//3.8/1.9						
RPM	1760//1460						
HZ	60//50	**PH**	3	**CL**	B		
SER.F.	1.00	**DES**	B	**CODE**	L		
RATING	40C AMB-CONT						
FRAME	145TC	**NEMA-NOM-EFF**	86.5				
PF	73						
BLANK							

AC Induction Motor Performance Data
Record # 78446
Typical performance - not guaranteed values

Winding: 35WGM493-R004	**Type:** 3526M	**Enclosure:** XPFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1.5//1	**Full Load Torque**	4.46 LB-FT
Volts			230/460//190/380	**Start Configuration**	direct on line
Full Load Amps			4.4/2.2//3.8/1.9	**Breakdown Torque**	21.1 LB-FT
R.P.M.			1760//1460	**Pull-up Torque**	10.5 LB-FT
Hz	60//50	**Phase**	3	**Locked-rotor Torque**	14.9 LB-FT
NEMA Design Code	B	**KVA Code**	L	**Starting Current**	19.3 A
Service Factor (S.F.)			1	**No-load Current**	1.52 A
NEMA Nom. Eff.	86.5	**Power Factor**	73	**Line-line Res. @ 25ºC**	10.1 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	45°C
				Locked-rotor Power Factor	51.5
				Rotor inertia	0.154 LB-FT2

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	29	48	63	73	79	84
Efficiency	73.9	83.2	86.3	86.9	86.5	85.5
Speed	1791	1782	1773	1763	1752	1740
Line amperes	1.57	1.72	1.93	2.22	2.57	2.93


ABB Motors and Mechanical Inc.

WINDING # 35WGM493


1.5 HP 3 PH 60 HZ 1763 RPM 460 V 3526M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=21.1 PU=10.5 LR=14.9 LRA=19.3




11/17/2026 ACPERF, record # 78446


35LYE377
510-520 = 14.34
521-528 = 15.21
529-535 = 16.09
536-546 = 17.46
4.72
2.25
(.13)
2.12
.12
.19 KEY
1.38 LONG
Ø7.19
Ø6.45
X-PROOF NAMEPLATE
BALDOR
PT. NO. 35CB3500
Ø4.500
4.497
Ø.8750
.8745
4.00
2.75
5.00
.50
5.94
6.71
6.92
45°
45°
7.10
3.50
3.44
4 HOLES
.38-16 TAP
.56 DEEP
ON 5.88 DIA. B.C.
LEAD HOLE
.75 N.P.T.
2.75
2.75
5.33
3.25
6.50
6 HOLES
.34 WIDE
.08
MIN.
.0015 MAX
CLEARANCE
.38
MIN.
.006
.004
.50
1.00
MIN.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: UPDATE NAMEPLATE BRACKET TO HA6000A07
REV: N
VERSION: 03
REVISED: 11:01:44 11/19/2021
TDR: 000001181686
MODEL NO. 35LYE377
REF: -
BY: USANEAT
B
BALDOR - RELIANCE®
STD HORZ NEMA 143-5TC XPFC X35M CL-I GP-D, CL-II GP-F&G
35LYE377

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS