ABB BALDOR RELIANCE

Customer information packet

CEM7063T-I-5

25HP, 3520RPM, 3PH, 60HZ, 284TSC, 1048M, XPFC
Class - CLI GP C,D
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 3:54:36 PM

Specifications

Enclosure	XPFC
Frame	284TSC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	25.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UL
	CSA
	CSA EEV
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	23.000 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater

Part Detail

Revision	T
Type	AC
Mech. spec.	10G898
Base	
Status	PRD/A
Elec. spec.	10WGZ277
Layout	10LYG898
Eff. date	11-22-2024
CD Diagram	CD0006
Poles	02
Leads	3#10
Proprietary	False
Created date	05-14-2014

High Voltage Full Load Amps	23.0 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	F
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X1048M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	27.23 IN
Power Factor	90
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3520 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP0977XPSLEV											
NO.						**CC**	010A				
SER.						**TEMP CODE**	T3C				
SPEC.	10G898Z277G1										
CAT.NO.	CEM7063T-I-5										
HP	25 NEMA MG-1 PT.5,IP55										
VOLTS	575										
AMPS	23										
RPM	3520				**MOTOR WEIGHT**		525				
HERTZ	60	**PH**	3	**CL**	F	**DE BRG**	6311				
SER.F.	1.15	**DES**	B	**CODE**	F	**ODE BRG**	6309				
FRAME	284TSC	**GREASE**	POLYREX EM								
RATING	40C AMB-CONT										
				NEMA-NOM-EFF		91.7	**PF**	90			
	55C AMB @ 1.0 SF,60C RISE										

AC Induction Motor Performance Data
Record # 45929
Typical performance - not guaranteed values

Winding: 10WGZ277-R002	**Type:** 1048M	**Enclosure:** XPFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			25	**Full Load Torque**	37.4 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			23	**Breakdown Torque**	101 LB-FT
R.P.M.			3520	**Pull-up Torque**	41.3 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	53 LB-FT
NEMA Design Code	B	**KVA Code**	F	**Starting Current**	134 A
Service Factor (S.F.)			1.15	**No-load Current**	5.48 A
NEMA Nom. Eff.	91.7	**Power Factor**	90	**Line-line Res. @ 25ºC**	0.46 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	57°C
S.F. Amps				**Temp. Rise @ S.F. Load**	71°C
				Locked-rotor Power Factor	23
				Rotor inertia	2.06 LB-FT2

Load Characteristics 575 V, 60 Hz, 25 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	69	83	88	90	90	90	90
Efficiency	87.9	91.6	92.3	91.8	91	89.8	91.3
Speed	3580	3563	3542	3520	3496	3468	3506
Line amperes	8.03	12.3	17.4	22.7	28.5	34.9	26.2


ABB Motors and Mechanical Inc.


WINDING # 10WGZ277

25 HP 3 PH 60 HZ 3520 RPM 575 V 1048M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=101 PU=41.3 LR=53 LRA=134





10LYG898
(1032-1060) = 27.24
13.74
3.00
.25
.38 KEY
1.88 LONG
Ø15.10
Ø11.23
Ø1.625
1.624
Ø10.500
10.497
SLINGER
DRAIN FITTING
HW4505A02
(EA. END)
8 HOLES
Ø.53
9.50
9.50
.88
11.00
4.76
12.75
15.39
16.53
7.58
PIPE PLUGS
(EA. END)
45°
45°
2.50
14.94
7.00 +.00 -.06
LEAD HOLE
1.50 NPT
HW3023E06
5.50
5.50
11.57
6.49
12.98
4 HOLES
.50-13 TAP ON
Ø9.00 B.C.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD MARKING FILE FOR STOCK PRODUCTS
REV: B
VERSION: 02
REVISED: 09:04:34 06/28/2023
TDR: 000001211833
MODEL NO. 10LYG898
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
HORZ XPFC 284-6TSC CL.I GP.C&D ONLY, DRILL RIG
10LYG898


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1