

ABB BALDOR RELIANCE III

Customer information packet

CEM7056T-I-5

20 NEMA MG-1 PT.5, IP55HP, 1770RPM, 3

Class - CLI GP C,D

Division - Division I

Specifications

Enclosure	XPFC
Frame	256TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	20.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	19.200 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	19.2 a

Part Detail

Revision	M
Type	AC
Mech. spec.	09F368
Base	
Status	PRD/A
Elec. spec.	09WGT507
Layout	09LYF368
Eff. date	02-21-2024
CD Diagram	CD0006
Poles	04
Leads	3#10
Proprietary	False
Created date	11-20-2017

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X0960M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	26.00 IN
Power Factor	83
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0977XPSLEV												
NO.							CC	010A				
SER.							TEMP CODE		T3C			
SPEC.	09F368T507G1											
CAT.NO.	CEM7056T-I-5											
HP	20 NEMA MG-1 PT.5,IP55											
VOLTS	575											
AMPS	19.2											
RPM	1770				MOTOR WEIGHT				339			
HERTZ	60	PH	3	CL	F	DE BRG	6309					
SER.F.	1.15	DES	A	CODE	J	ODE BRG			6208			
FRAME	256TC		GREASE		POLYREX EM							
RATING	40C AMB-CONT											
				NEMA-NOM-EFF				93		PF	83	
	55C AMB @ 1.0 SF,60C RISE											

AC Induction Motor Performance Data

Record # 68077

Typical performance - not guaranteed values

Winding: 09WGT507-R004			Type: 0960M		Enclosure: XPFC		
Nameplate Data			575 V, 60 Hz: Single Voltage Motor				
Rated Output (HP)		20	Full Load Torque		59.29 LB-FT		
Volts		575	Start Configuration		direct on line		
Full Load Amps		19.2	Breakdown Torque		231 LB-FT		
R.P.M.		1770	Pull-up Torque		126 LB-FT		
Hz	60 Phase	3	Locked-rotor Torque		140 LB-FT		
NEMA Design Code		A	KVA Code		J	Starting Current	158 A
Service Factor (S.F.)		1.15	No-load Current		8.28 A		
NEMA Nom. Eff.		93	Power Factor		83	Line-line Res. @ 25°C	0.499 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		58°C
S.F. Amps					Temp. Rise @ S.F. Load		69°C
					Locked-rotor Power Factor		26.5
					Rotor inertia		2.65 LB-FT2

Load Characteristics 575 V, 60 Hz, 20 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	45	67	78	83	86	87	85
Efficiency	89.2	93	93.7	93.5	93.1	92.4	93.3
Speed	1793	1786	1779	1772	1764	1755	1767
Line amperes	9.41	11.99	15.34	19.19	23.44	27.92	21.7


ABB Motors and Mechanical Inc.


WINDING # 09WGT507

Typical performance - not guaranteed values.




20 HP 3 PH 60 HZ 1770 RPM 575 V 0960M

TORQUES (LB-FT): PO=231 PU=126 LR=140 LRA=158





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: —


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1