

ABB BALDOR RELIANCE III

Customer information packet

CEM7060T-I-5

30HP, 1770RPM, 3PH, 60HZ, 286TC, 1056M, XPFC, F

Class - CLI GP C,D

Division - Division I

Specifications

Enclosure	XPFC
Frame	286TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UL CSA CSA EEV UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	29.000 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.6 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater

Part Detail

Revision	AF
Type	AC
Mech. spec.	10E949
Base	
Status	PRD/A
Elec. spec.	10WGY759
Layout	10LYE949
Eff. date	11-22-2024
CD Diagram	CD0006
Poles	04
Leads	3#10
Proprietary	False
Created date	07-31-2012

High Voltage Full Load Amps	29.0 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X1056M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	28.61 IN
Power Factor	83
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP0977XPSLEV												
NO.							CC	010A				
SER.							TEMP CODE	T3C				
SPEC.	10E949Y759G1											
CAT.NO.	CEM7060T-I-5											
HP	30 NEMA MG-1 PT.5,IP55											
VOLTS	575											
AMPS	29											
RPM	1770				MOTOR WEIGHT				550			
HERTZ	60	PH	3	CL	F	DE BRG	6311					
SER.F.	1.15	DES	A	CODE	G	ODE BRG			6309			
FRAME	286TC		GREASE		POLYREX EM							
RATING	40C AMB-CONT											
				NEMA-NOM-EFF				93.6		PF	83	
	55C AMB @ 1.0 SF 60C RISE											

AC Induction Motor Performance Data

Record # 53265

Typical performance - not guaranteed values

Winding: 10WGY759-R012			Type: 1056M	Enclosure: XPFC	
Nameplate Data			575 V, 60 Hz: Single Voltage Motor		
Rated Output (HP)		30	Full Load Torque		89.2 LB-FT
Volts		575	Start Configuration		direct on line
Full Load Amps		29	Breakdown Torque		255 LB-FT
R.P.M.		1770	Pull-up Torque		120 LB-FT
Hz	60	Phase	3	Locked-rotor Torque	136 LB-FT
NEMA Design Code	B	KVA Code	G	Starting Current	177 A
Service Factor (S.F.)		1.15	No-load Current		11.5 A
NEMA Nom. Eff.	93.6	Power Factor	83	Line-line Res. @ 25°C	0.375 Ω
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		58°C
S.F. Amps			Temp. Rise @ S.F. Load		71°C
			Locked-rotor Power Factor		32
			Rotor inertia		4.45 LB-FT2

Load Characteristics 575 V, 60 Hz, 30 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	47	69	77	84	84	83	84
Efficiency	90.9	93.9	94.4	94	92.9	92.5	93.4
Speed	1794	1786	1780	1773	1764	1754	1768
Line amperes	13.3	17.6	23.4	28.5	35.9	43.6	32.9


ABB Motors and Mechanical Inc.


WINDING # 10WGY759

Typical performance - not guaranteed values.




30 HP 3 PH 60 HZ 1770 RPM 575 V 1056M

TORQUES (LB-FT): PO=255 PU=120 LR=136 LRA=177





CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: —



BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1