Customer information packet

CESSWDM3546-5

1HP, 1775RPM, 3PH, 60HZ, 56C, 3522M, TENV, F1, N
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/16/2026 11:57:42 PM

Specifications

Enclosure	TENV
Frame	56C
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.300 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	85.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.3 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	N

Part Detail

Revision	D
Type	AC
Mech. spec.	35W899
Base	
Status	PRD/A
Elec. spec.	35WGG198
Layout	35LYW899
Eff. date	02-19-2024
CD Diagram	CD0006
Poles	04
Leads	3#18 Y
Proprietary	False
Created date	03-11-2022

Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3522M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	11.09 IN
Power Factor	67
Product Family	Wash Down All Stainless Steel
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1951A05									
CAT.NO.	CESSWDM3546-5								
SPEC.	35W899G198G1								
HP	1								
VOLTS	575								
AMP	1.3								
RPM	1775								
FRAME	56C		**HZ**	60			**PH**	3	
SER.F.	1.15	**CODE**	M	**DES**	B	**CLASS**		F	
NEMA-NOM-EFF	85.5		**PF**	70					
RATING	40C AMB-CONT								
CC	010A								
DE	6205		**ODE**	6203					
ENCL	TENV	**SN**							
	SFA 1.4								

AC Induction Motor Performance Data
Record # 82151
Typical performance - not guaranteed values

Winding: 35WGG198-R001	**Type:** 3522M	**Enclosure:** TEFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			1	**Full Load Torque**	2.99 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			1.3	**Breakdown Torque**	16.37 LB-FT
R.P.M.			1770	**Pull-up Torque**	7.31 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	10.16 LB-FT
NEMA Design Code	B	**KVA Code**	N	**Starting Current**	12.72 A
Service Factor (S.F.)			1.15	**No-load Current**	0.972 A
NEMA Nom. Eff.	85.5	**Power Factor**	67	**Line-line Res. @ 25ºC**	22.9 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	63°C
S.F. Amps			1.4	**Temp. Rise @ S.F. Load**	71°C
				Locked-rotor Power Factor	59.6
				Rotor inertia	0.159 lb-ft²

Load Characteristics 575 V, 60 Hz, 1 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	28	44	56	67	73	78	71
Efficiency	71.2	81.2	84.4	86	85.7	85.1	85.8
Speed	1793	1786	1781	1773	1766	1757	1769
Line amperes	0.988	1.06	1.18	1.32	1.49	1.69	1.42


ABB Motors and Mechanical Inc.

WINDING # 35WGG198


1 HP 3 PH 60 HZ 1770 RPM 575 V 3522M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=16.37 PU=7.31 LR=10.16 LRA=12.72





11/16/2026 ACPERF, record # 82151


35LYW899
510-524 = 11.09
2.06
.13
1.88
LASER ETCHED WARNING LABEL
LASER ETCHED NP
.19 KEY
1.38 LONG
Ø6.50
Ø4.500
4.497
Ø.6250
.6245
4 SLOTS
.34 WIDE
2.82
3.00
2.75
.75
4.50
4 HOLES
3 W/ PLUGS
EA. END
Ø6.63
5.86
45°
45°
TOP OF NP
& WARNING
LABEL
6.78
3.50
3.44
4 HOLES
.38-16 TAP ON
Ø5.88 DIA. B.C.
LEAD HOLE
.50 N.P.T.
2.44
2.44
4.77
3.25
6.50
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD INOPC CREATED SWD DRG INTO BUS - PACKAGE 29
REV: A
VERSION: 01
REVISED: 09:39:16 07/26/2019
TDR: 000001114730
MODEL NO. 35LYW899
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
HOR 56C TENV M WD4, LK'D PU BRG, LASER ETCH BAND (510-524)
SH 1 of 1
35LYW899


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1