

ABB BALDOR RELIANCE III

Customer information packet

CESSWDM3546-5

1HP, 1775RPM, 3PH, 60HZ, 56C, 3522M, TENV, F1, N

Class - None

Division - Not Applicable

Specifications

Enclosure	TENV
Frame	56C
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.300 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	85.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.3 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	N

Part Detail

Revision	D
Type	AC
Mech. spec.	35W899
Base	
Status	PRD/A
Elec. spec.	35WGG198
Layout	35LYW899
Eff. date	02-19-2024
CD Diagram	CD0006
Poles	04
Leads	3#18 Y
Proprietary	False
Created date	03-11-2022

Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3522M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	11.09 IN
Power Factor	67
Product Family	Wash Down All Stainless Steel
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1951A05											
CAT.NO.	CESSWDM3546-5										
SPEC.	35W899G198G1										
HP	1										
VOLTS	575										
AMP	1.3										
RPM	1775										
FRAME	56C		HZ	60				PH	3		
SER.F.	1.15		CODE	M	DES	B		CLASS	F		
NEMA-NOM-EFF	85.5		PF	70							
RATING	40C AMB-CONT										
CC	010A										
DE	6205		ODE	6203							
ENCL	TENV	SN									
	SFA 1.4										

AC Induction Motor Performance Data

Record # 82151

Typical performance - not guaranteed values

Winding: 35WGG198-R001			Type: 3522M		Enclosure: TEFC	
Nameplate Data			575 V, 60 Hz: Single Voltage Motor			
Rated Output (HP)		1	Full Load Torque			2.99 LB-FT
Volts		575	Start Configuration			direct on line
Full Load Amps		1.3	Breakdown Torque			16.37 LB-FT
R.P.M.		1770	Pull-up Torque			7.31 LB-FT
Hz	60	Phase	3	Locked-rotor Torque		10.16 LB-FT
NEMA Design Code	B	KVA Code	N	Starting Current		12.72 A
Service Factor (S.F.)		1.15	No-load Current			0.972 A
NEMA Nom. Eff.	85.5	Power Factor	67	Line-line Res. @ 25°C		22.9 Ω
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load			63°C
S.F. Amps		1.4	Temp. Rise @ S.F. Load			71°C
			Locked-rotor Power Factor			59.6
			Rotor inertia			0.159 lb-ft²

Load Characteristics 575 V, 60 Hz, 1 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	28	44	56	67	73	78	71
Efficiency	71.2	81.2	84.4	86	85.7	85.1	85.8
Speed	1793	1786	1781	1773	1766	1757	1769
Line amperes	0.988	1.06	1.18	1.32	1.49	1.69	1.42


ABB Motors and Mechanical Inc.


WINDING # 35WGG198

Typical performance - not guaranteed values.



1 HP 3 PH 60 HZ 1770 RPM 575 V 3522M

TORQUES (LB-FT): PO=16.37 PU=7.31 LR=10.16 LRA=12.72





CD0006



- NOTES:
1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
 2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
 5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10: 24: 49 02/19/2019	BY: ENBRIRO
MTL: —		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1