ABB BALDOR RELIANCE

Customer information packet

CESSWDM3714T-5

10HP, 1770RPM, 3PH, 60HZ, 215TC, 3754M, TEFC, F
Class -
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/16/2026 12:37:47 PM

Specifications

Enclosure	TEFC
Frame	215TC
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	9.800 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	9.8 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing

Part Detail

Revision	G
Type	AC
Mech. spec.	37J639
Base	
Status	PRD/A
Elec. spec.	37WGR528
Layout	37LYJ639
Eff. date	12-18-2024
CD Diagram	CD0006
Poles	04
Leads	3#14
Proprietary	False
Created date	11-21-2017

Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3754M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	21.66 IN
Power Factor	84
Product Family	Wash Down All Stainless Steel
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1953C05							
CAT.NO.	CESSWDM3714T-5						
SPEC.	37J639R528G1						
HP	10						
VOLTS	575						
AMP	9.8						
RPM	1770						
FRAME	215TC	**HZ**	60			**PH**	3
SER.F.	1.15	**CODE**	H	**DES**	B	**CLASS**	F
NEMA-NOM-EFF	91.7	**PF**	84				
RATING	40C AMB-CONT						
CC	010A	**USABLE AT 208V**				N/A	
DE	6307	**ODE**	6206				
ENCL	TEFC	**SN**					
	4:1CT 20:1VT						

AC Induction Motor Performance Data
Record # 42939
Typical performance - not guaranteed values

Winding: 37WGR528-R001	**Type:** 3754M	**Enclosure:** TEFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			10	**Full Load Torque**	30 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			9.8	**Breakdown Torque**	76.7 LB-FT
R.P.M.			1770	**Pull-up Torque**	45.1 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	51.4 LB-FT
NEMA Design Code	B	**KVA Code**	H	**Starting Current**	66.9 A
Service Factor (S.F.)			1.15	**No-load Current**	3.57 A
NEMA Nom. Eff.	91.7	**Power Factor**	84	**Line-line Res. @ 25ºC**	1.56 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	68°C
S.F. Amps				**Temp. Rise @ S.F. Load**	84°C

Load Characteristics 575 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	49	72	80	84	85	86	85
Efficiency	88.9	91.9	92.4	92.1	90.9	89.8	91.4
Speed	1791	1783	1775	1764	1755	1743	1759
Line amperes	4.2	5.62	7.58	9.78	12.1	14.6	11.2


ABB Motors and Mechanical Inc.

WINDING # 37WGR528


10 HP 3 PH 60 HZ 1770 RPM 575 V 3754M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=76.7 PU=45.1 LR=51.4 LRA=66.9





11/16/2026 ACPERF, record # 42939


37LYJ639
(717-735) = 18.94
(736-744) = 20.07
(745-750) = 20.82
(751-756) = 21.57
5.32
LASER ETCHED WARNING LABEL
LASER ETCHED NP
3.12
.25
.31 KEY 2.38 LONG
9.07
8.500
8.497
Ø1.3750
1.3745
4 HOLES 3 W/PLUGS (EA. END)
6 HOLES .44 DIA.
5.50
.50
7.00
4.50
8.00
9.56
8.59
4.78
45°
45°
TOP OF NP & WARNING LABEL
2.39
10.03
4 HOLES .50-13 TAP ON Ø7.25 B.C.
5.25 +.00 -.06
LEAD HOLE .75 N.P.T.
4.25
4.25
7.37
4.75
9.50
FRONT END DETAIL
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD DRAWING TO SOLIDWORKS
REV: A VERSION: 01 REVISED: 11:49:02 06/14/2022 TDR: 000001192277
MODEL NO. 37LYJ639 REF: -
BY: ENALEM0 B
BALDOR
STD HOR 213-5TC TEFC 37M WD4 W/LASER ETCHED BAND
37LYJ639


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007			BALDOR - RELIANCE®
REV. LTR: E	VERSION: 01	TDR: 000001099922	
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0	3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED
MTL: –			SH 1 of 1