

# ABB BALDOR RELIANCE III

---

## Customer information packet

### CEWDBM3542

.75HP, 1765RPM, 3PH, 60HZ, 56C, 3514M, TENV, F1

Class - None

Division - Not Applicable

**Specifications**

|                                |                                                             |
|--------------------------------|-------------------------------------------------------------|
| Enclosure                      | TENV                                                        |
| Frame                          | 56C                                                         |
| Frame Material                 | Steel                                                       |
| Frequency                      | 60.00 Hz                                                    |
| Haz Area Class and Group       | None                                                        |
| Haz Area Division              | Not Applicable                                              |
| Motor Letter Type              | Three Phase                                                 |
| Output @ Frequency             | .750 HP @ 60 HZ                                             |
| Phase                          | 3                                                           |
| Synchronous Speed @ Frequency  | 1800 RPM @ 60 HZ                                            |
| Voltage @ Frequency            | 230.0 V @ 60 HZ<br>460.0 V @ 60 HZ                          |
| Agency Approvals               | CSA<br>UR                                                   |
| Ambient Temperature            | 40 °C                                                       |
| Auxiliary Box                  | NO AUXILLARY BOX                                            |
| Auxiliary Box Lead Termination | None                                                        |
| Base Indicator                 | Rigid                                                       |
| Bearing Grease Type            | Polyrex EM (-20F +300F)                                     |
| Blower                         | None                                                        |
| Current @ Voltage              | 1.140 A @ 460.0 V<br>2.280 A @ 230.0 V<br>2.400 A @ 208.0 V |
| Design Code                    | B                                                           |
| Drip Cover                     | No Drip Cover                                               |
| Duty Rating                    | CONT                                                        |
| Efficiency @ 100% Load         | 82.5 %                                                      |
| Electrically Isolated Bearing  | Not Electrically Isolated                                   |
| Feedback Device                | NO FEEDBACK                                                 |
| Front Shaft Indicator          | None                                                        |
| Heater Indicator               | No Heater                                                   |
| High Voltage Full Load Amps    | 1.1 a                                                       |

**Part Detail**

|              |            |
|--------------|------------|
| Revision     | F          |
| Type         | AC         |
| Mech. spec.  | 35L652     |
| Base         |            |
| Status       | PRD/A      |
| Elec. spec.  | 35WGG069   |
| Layout       | 35LYL652   |
| Eff. date    | 06-27-2024 |
| CD Diagram   | CD0005     |
| Poles        | 04         |
| Leads        | 9#18       |
| Proprietary  | False      |
| Created date | 01-10-2022 |

|                                      |                            |
|--------------------------------------|----------------------------|
| <b>Insulation Class</b>              | <b>F</b>                   |
| <b>Inverter Code</b>                 | <b>Not Inverter</b>        |
| <b>KVA Code</b>                      | <b>K</b>                   |
| <b>Lifting Lugs</b>                  | <b>No Lifting Lugs</b>     |
| <b>Locked Bearing Indicator</b>      | <b>Locked Bearing</b>      |
| <b>Motor Lead Quantity/Wire Size</b> | <b>9 @ 18 AWG</b>          |
| <b>Motor Lead Termination</b>        | <b>Flying Leads</b>        |
| <b>Motor Standards</b>               | <b>NEMA</b>                |
| <b>Motor Type</b>                    | <b>3514M</b>               |
| <b>Mounting Arrangement</b>          | <b>F1</b>                  |
| <b>Number of Poles</b>               | <b>4</b>                   |
| <b>Overall Length</b>                | <b>15.31 IN</b>            |
| <b>Power Factor</b>                  | <b>74</b>                  |
| <b>Product Family</b>                | <b>Wash Down</b>           |
| <b>Pulley End Bearing Type</b>       | <b>Sealed Bearing</b>      |
| <b>Pulley Face Code</b>              | <b>C-Face</b>              |
| <b>Pulley Shaft Indicator</b>        | <b>Standard</b>            |
| <b>Rodent Screen</b>                 | <b>None</b>                |
| <b>Service Factor</b>                | <b>1.25</b>                |
| <b>Shaft Diameter</b>                | <b>0.625 IN</b>            |
| <b>Shaft Ground Indicator</b>        | <b>No Shaft Grounding</b>  |
| <b>Shaft Rotation</b>                | <b>Reversible</b>          |
| <b>Shaft Slinger Indicator</b>       | <b>Shaft Slinger</b>       |
| <b>Speed</b>                         | <b>1765 rpm</b>            |
| <b>Speed Code</b>                    | <b>Single Speed</b>        |
| <b>Starting Method</b>               | <b>Direct on line</b>      |
| <b>Thermal Device - Bearing</b>      | <b>None</b>                |
| <b>Thermal Device - Winding</b>      | <b>None</b>                |
| <b>Vibration Sensor Indicator</b>    | <b>No Vibration Sensor</b> |
| <b>Winding Thermal 1</b>             | <b>None</b>                |
| <b>Winding Thermal 2</b>             | <b>None</b>                |

Nameplate

| NP2179L      |               |  |      |      |     |   |  |       |   |  |  |
|--------------|---------------|--|------|------|-----|---|--|-------|---|--|--|
| CAT.NO.      | CEWDBM3542    |  |      |      |     |   |  |       |   |  |  |
| SPEC.        | 35L652G069G1  |  |      |      |     |   |  |       |   |  |  |
| HP           | .75           |  |      |      |     |   |  |       |   |  |  |
| VOLTS        | 230/460       |  |      |      |     |   |  |       |   |  |  |
| AMP          | 2.4/1.2       |  |      |      |     |   |  |       |   |  |  |
| RPM          | 1765          |  |      |      |     |   |  |       |   |  |  |
| FRAME        | 56C           |  | HZ   | 60   |     |   |  | PH    | 3 |  |  |
| SER.F.       | 1.25          |  | CODE | K    | DES | B |  | CLASS | F |  |  |
| NEMA-NOM-EFF | 82.5          |  | PF   | 74   |     |   |  |       |   |  |  |
| RATING       | 40C AMB-CONT  |  |      |      |     |   |  |       |   |  |  |
| CC           |               |  |      |      |     |   |  |       |   |  |  |
| DE           | 6205          |  | ODE  | 6203 |     |   |  |       |   |  |  |
| ENCL         | TENV          |  | SN   |      |     |   |  |       |   |  |  |
| BLANK        | SFA 2.68/1.34 |  |      |      |     |   |  |       |   |  |  |

**AC Induction Motor Performance Data**

Record # 87322

Typical performance - not guaranteed values

| Winding: 35WGG069-R009 |    |           | Type: 3514M                              |                     | Enclosure: TENV         |                       |        |
|------------------------|----|-----------|------------------------------------------|---------------------|-------------------------|-----------------------|--------|
| Nameplate Data         |    |           | 460 V, 60 Hz:<br>High Voltage Connection |                     |                         |                       |        |
| Rated Output (HP)      |    | .75       | Full Load Torque                         |                     | 2.24 LB-FT              |                       |        |
| Volts                  |    | 230/460   | Start Configuration                      |                     | direct on line          |                       |        |
| Full Load Amps         |    | 2.42/2.42 | Breakdown Torque                         |                     | 8 LB-FT                 |                       |        |
| R.P.M.                 |    | 1765      | Pull-up Torque                           |                     | 4.4 LB-FT               |                       |        |
| Hz                     | 60 | Phase     | 3                                        | Locked-rotor Torque |                         | 5.1 LB-FT             |        |
| NEMA Design Code       |    | B         | KVA Code                                 | K                   |                         | Starting Current      | 8.4 A  |
| Service Factor (S.F.)  |    | 1.25      | No-load Current                          |                     | 0.85 A                  |                       |        |
| NEMA Nom. Eff.         |    | 82.5      | Power Factor                             | 74                  |                         | Line-line Res. @ 25°C | 30.3 Ω |
| Rating - Duty          |    | 40C       | AMB-CONT                                 |                     | Temp. Rise @ Rated Load |                       | 75°C   |
| S.F. Amps              |    | 2.8/1.4   | Temp. Rise @ S.F. Load                   |                     | 94°C                    |                       |        |
|                        |    |           | Locked-rotor Power Factor                |                     | 66.8                    |                       |        |
|                        |    |           | Rotor inertia                            |                     | 0.101 lb-ft²            |                       |        |

**Load Characteristics 460 V, 60 Hz, 0.75 HP**

| % of Rated Load | 25   | 50   | 75   | 100  | 125  | 150  | S.F. |
|-----------------|------|------|------|------|------|------|------|
| Power Factor    | 30   | 48   | 61   | 70   | 77   | 81   | 80   |
| Efficiency      | 68.4 | 79   | 82.2 | 82.9 | 82.4 | 81.2 | 82.8 |
| Speed           | 1791 | 1783 | 1775 | 1766 | 1757 | 1746 | 1752 |
| Line amperes    | 0.87 | 0.95 | 1.06 | 1.21 | 1.4  | 1.61 | 1.34 |


ABB Motors and Mechanical Inc.

WINDING # 35WGG069

0.75 HP 3 PH 60 HZ 1765 RPM 460 V 3514M

Typical performance - not guaranteed values.

TORQUES (LB-FT) : PO=8 PU=4.4 LR=5.1 LRA=8.4



8/29/2026 ACPERF, record # 87322



