

ABB BALDOR RELIANCE III

Customer information packet

CEWDM3554-H

1.5HP, 1770RPM, 3PH, 60HZ, 56HC, 3530M, TENV, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TENV
Frame	56HC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA EEV UR NEMA_PREMIUM NEMA PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.100 A @ 460.0 V 4.200 A @ 230.0 V 4.400 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater

Part Detail

Revision	B
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	35WGG178
Layout	35LY-000-259
Eff. date	02-14-2024
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	10-28-2021

High Voltage Full Load Amps	2.1 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3530M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	11.91 IN
Power Factor	76
Product Family	Wash Down
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L											
CAT.NO.	CEWDM3554-H										
SPEC.	35-0000-1384										
HP	1.5										
VOLTS	230/460										
AMP	4.2/2.1										
RPM	1770										
FRAME	56HC		HZ	60				PH	3		
SER.F.	1.00	CODE	N	DES	B			CLASS	H		
NEMA-NOM-EFF	86.5	PF	76								
RATING	40C AMB-CONT										
CC	010A										
DE	6205		ODE	6203							
ENCL	TENV	SN									
BLANK											

AC Induction Motor Performance Data

Record # 87056

Typical performance - not guaranteed values

Winding: 35WGG178-R003			Type: 3530M		Enclosure: TENV		
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		1.5		Full Load Torque		4.48 LB-FT	
Volts		230/460		Start Configuration		direct on line	
Full Load Amps		4.6/2.3		Breakdown Torque		21.02 LB-FT	
R.P.M.		1770		Pull-up Torque		12.29 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		14.9 LB-FT	
NEMA Design Code		B	KVA Code	M	Starting Current		21.32 A
Service Factor (S.F.)		1		No-load Current		1.29 A	
NEMA Nom. Eff.		86.5	Power Factor	72	Line-line Res. @ 25°C		10.1 Ω
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load	80°C
				Locked-rotor Power Factor		55.5	
				Rotor inertia		0.217 lb-ft²	

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	33	54	68	76	81	84
Efficiency	79.1	86.3	88.1	88.3	87.6	86.6
Speed	1790	1783	1776	1769	1761	1752
Line amperes	1.35	1.52	1.78	2.11	2.47	2.89


ABB Motors and Mechanical Inc.

WINDING # 35WGG178


Typical performance - not guaranteed values.

1.5 HP 3 PH 60 HZ 1770 RPM 460 V 3530M

TORQUES (LB-FT): PO=21.02 PU=12.29 LR=14.9 LRA=21.32



35LY-000-259



PULLEY END DETAIL

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: UPDATE MATE ERRORS IN 3D MODEL

REV: A	VERSION: 01	REVISED: 08:47:50 04/21/2022	TDR: 000001188385
--------	-------------	------------------------------	-------------------

657-000-1759

MODEL NO. 35LY-000-259

BY: USBUFRA

REF: -

BALDOR - RELIANCE®

STD HORZ 56HC TENV 35M WD

35LY-000-259

