

ABB BALDOR RELIANCE III

Customer information packet

CEWDM3617T

1HP, 850RPM, 3PH, 60HZ, 182TC, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	182TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	900 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA UR NEMA PREMIUM CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.300 A @ 460.0 V 4.600 A @ 208.0 V 4.600 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	75.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater

Part Detail

Revision	B
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	36WGR622
Layout	36LYK190
Eff. date	02-14-2024
CD Diagram	CD0005
Poles	08
Leads	9#16
Proprietary	False
Created date	01-07-2020

High Voltage Full Load Amps	2.3 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3628M
Mounting Arrangement	F1
Number of Poles	8
Overall Length	16.54 IN
Power Factor	52
Product Family	Wash Down
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	850 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L									
CAT.NO.	CEWDM3617T								
SPEC.	36-0000-0264								
HP	1								
VOLTS	230/460								
AMP	4.6/2.3								
RPM	850								
FRAME	182TC		HZ	60			PH	3	
SER.F.	1.15	CODE	L	DES	B	CLASS	F		
NEMA-NOM-EFF	75.5	PF	52						
RATING	40C AMB-CONT								
CC	010A								
DE	6206		ODE	6205					
ENCL	TEFC	SN							
BLANK	10:1CT, 10:1VT, 1.00 SF								

AC Induction Motor Performance Data

Record # 78114

Typical performance - not guaranteed values

Winding: 36WGR622-R010			Type: 3628M		Enclosure: TEFC	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		1	Full Load Torque		6.26 LB-FT	
Volts		230/460	Start Configuration		direct on line	
Full Load Amps		4.6/2.3	Breakdown Torque		19.8 LB-FT	
R.P.M.		850	Pull-up Torque		12.1 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque	15.7 LB-FT	
NEMA Design Code	B	KVA Code	L	Starting Current	9.52 A	
Service Factor (S.F.)		1.15	No-load Current		1.55 A	
NEMA Nom. Eff.	75.5	Power Factor	52	Line-line Res. @ 25°C	15.1 Ω	
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		62°C	
S.F. Amps			Temp. Rise @ S.F. Load		72°C	
			Locked-rotor Power Factor		47.6	
			Rotor inertia		0.263 LB-FT2	

Load Characteristics 460 V, 60 Hz, 1 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	26	39	51	60	66	71	64
Efficiency	60.2	71.7	75.3	75.9	74.6	72	75.1
Speed	890	879	868	855	840	822	846
Line amperes	1.57	1.69	1.87	2.09	2.39	2.77	2.27

ABB Motors and Mechanical Inc.

WINDING # 36WGR622

Typical performance - not guaranteed values.

1 HP 3 PH 60 HZ 850 RPM 460 V 3628M

TORQUES (LB-FT): PO=19.8 PU=12.1 LR=15.7 LRA=9.52





