

ABB BALDOR RELIANCE III

Customer information packet

CEWDM4112T

20HP, 880RPM, 3PH, 60HZ, 324TC, 1256M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	324TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	20.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	900 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	62.000 A @ 208.0 V 60.000 A @ 230.0 V 30.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	90.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part Detail

Revision	B
Type	AC
Mech. spec.	12P032
Base	
Status	PRD/A
Elec. spec.	12WGZ306
Layout	12LYP032
Eff. date	02-14-2024
CD Diagram	CD0005
Poles	08
Leads	9#10
Proprietary	False
Created date	04-18-2023

Heater Indicator	No Heater
High Voltage Full Load Amps	30.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1256M
Mounting Arrangement	F1
Number of Poles	8
Overall Length	30.28 IN
Power Factor	68
Product Family	Washdown Features
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	880 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L									
CAT.NO.	CEWDM4112T								
SPEC.	12P032Z306								
HP	20								
VOLTS	230/460								
AMP	60/30								
RPM	880								
FRAME	324TC		HZ	60			PH	3	
SER.F.	1.15	CODE	G	DES	B	CLASS	F		
NEMA-NOM-EFF	90.2	PF	68						
RATING	40C AMB-CONT								
CC	010A								
DE	6312		ODE	6311					
ENCL	TEFC	SN							
BLANK	10:1 CT/VT								

AC Induction Motor Performance Data

Record # 92443

Typical performance - not guaranteed values

Winding: 12WGZ306-R001				Type: 1256M		Enclosure: TEFC	
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		20		Full Load Torque		119 LB-FT	
Volts		230/460		Start Configuration		direct on line	
Full Load Amps		60/30		Breakdown Torque		278 LB-FT	
R.P.M.		880		Pull-up Torque		156 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		164 LB-FT	
NEMA Design Code		B	KVA Code	G	Starting Current		141 A
Service Factor (S.F.)		1.15		No-load Current		17.47 A	
NEMA Nom. Eff.		90.2	Power Factor	68	Line-line Res. @ 25°C		0.37 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		56°C	
S.F. Amps				Temp. Rise @ S.F. Load		68°C	
				Locked-rotor Power Factor		34	
				Rotor inertia		7.46 lb-ft²	

Load Characteristics 460 V, 60 Hz, 20 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	30	49	61	68	72	73	68
Efficiency	85	90.1	91	90.7	89.9	88.5	90.4
Speed	894	890	885	881	875	868	878
Line amperes	18.32	20.94	25.08	30.17	36.38	43.47	34.9

ABB Motors and Mechanical Inc.

WINDING # 12WGZ306

Typical performance - not guaranteed values.

20 HP 3 PH 60 HZ 880 RPM 460 V 1256M

TORQUES (LB-FT): PO=278 PU=156 LR=164 LRA=141



