ABB BALDOR RELIANCE

Customer information packet

CEWDM4308T

40HP, 1190RPM, 3PH, 60HZ, 364TC, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 1:00:40 AM

Specifications

Enclosure	TEFC
Frame	364TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	40.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	99.600 A @ 230.0 V
	49.800 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	49.8 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	IP55
KVA Code	G

Part Detail

Revision	A
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG1194
Layout	617428-348
Eff. date	10-01-2021
CD Diagram	416820-002
Poles	06
Leads	3#4,6#6
Proprietary	False
Created date	08-22-2019

Lifting Lugs	Standard Lifting Lugs
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A36062M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	33.48 IN
Power Factor	80
Product Family	Washdown Features
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Service Factor	1.15
Shaft Diameter	2.374 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1190 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP2496L
MOBIL POLYREX EM

NP2428L												
SPEC NO.	A36-7821-1194	**CAT.NO.**	CEWDM4308T						**FRAME**	364TC		
HP	40	**VOLTS**	230/460	**PHASE**	3	**DESIGN**	B	**TYPE**	P			
RPM	1190	**AMPS**	99.6/49.8	**HZ**	60	**AMB**	40	**SF**	1.15			
DRIVE END BEARING	65BC03JGG30A	**DUTY**	CONT	**INSUL.CLASS**	F							
OPP D.E. BEARING	65BC03JGG30A	**ENCL**	TEFC	**CODE**	G							
SER.NO.		**POWER FACTOR**	80	**NEMA-NOM-EFFICIENCY**	94.1							
		MAX CORR KVAR	12	**GUARANTEED EFFICIENCY**	93							
	IP55	**NEMA NOM/CSA QUOTED EFF**										
	10:1CT AND 10:1VT ON VPWM INVE	RTER, 1.00SF	**MOTOR WEIGHT**	914								

REL. S.O.	FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS
	364TC	40	P	3/60	1190	230/460

AMPS	DUTY	AMB °C/ INSUL.	S.F.	NEMA DESIGN	CODE LETTER	ENCL.
99.6/49.8	CONT	40/F	1.15	B	G	TEFC

E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES.@25 °C OHMS (BETWEEN LINES)
491378	418141088JE	---	---	.0373/.149

PERFORMANCE

LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY
NO LOAD	0	18.5	1200	5.70	0
1/4	10.0	22.4	1197	47.0	89.2
2/4	20.0	29.6	1194	67.8	93.2
3/4	30.0	39.1	1191	76.3	94.1
4/4	40.0	49.8	1188	79.9	94.1
5/4	50.0	61.2	1184	81.6	93.7

SPEED TORQUE

	RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES
LOCKED ROTOR	0	165	291	300
PULL UP	480	142	251	274
BREAKDOWN	1134	251	444	172
FULL LOAD	1188	100	177	49.8

AMPERES SHOWN FOR 460. VOLT CONNECTION. IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE

REMARKS: TYPICAL DATA
XE MOTOR-NEMA NOM. EFF. 94.1 %
GUARANTEED MIN. EFF. 93.0%


BALDOR
A MEMBER OF THE ABB GROUP

DR. BY T.G. KELATI
CK. BY D. H. MAY
APP. BY E.J.CHRISTIAN
DATE 10/12/06

A-C MOTOR PERFORMANCE DATA A36WG1194-R013
ISSUE DATE 01/13/21

C/R 312091

REL S.O.	RPM 1190	S.F. 1.15	ROTOR 418141088JE
FRAME 364TC	VOLTS 230/460	NEMA DESIGN B	TEST S.O. TYPICAL DATA
HP 40	AMPS 99.6/49.8	CODE LETTER G	TEST DATE ---
TYPE P	DUTY CONT	ENCLOSURE TEFC	STATOR RES.@ 25 °C .0373/.149
PHASE/HERTZ 3/60	AMB °C/INSUL 40/F	E/S 491378	OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

BALDOR
A MEMBER OF THE ABB GROUP

DR. BY	T.G. KELATI
CK. BY	D. H. MAY
APP. BY	E.J.CHRISTIAN
DATE	10/12/06

A–C MOTOR PERFORMANCE CURVES


A36WG1194-R013

ISSUE DATE 01/13/21

C/R 312091

Printed on 1/13/21 9:25 @ bengap01.baldor.com

REL. S.O.		RPM	1190	S.F.	1.15	ROTOR	418141088JE
FRAME	364TC	VOLTS	230/460	NEMA DESIGN	B	TEST S.O.	TYPICAL DATA
HP	40	AMPS	99.6/49.8	CODE LETTER	G	TEST DATE	---
TYPE	P	DUTY	CONT	ENCLOSURE	TEFC	STATOR RES.@ 25 °C	.0373/.149
PHASE/HERTZ	3/60	AMB °C/INSUL	40/F	E/S	491378		OHMS (BETWEEN LINES)



REMARKS:

THERMAL LIMIT CURVE

XE MOTOR-NEMA NOM. EFF. 94.1 %

GUARANTEED MIN. EFF. 93.0%

AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

BALDOR A MEMBER OF THE ABB GROUP

DR. BY	T.G. KELATI
CK. BY	D. H. MAY
APP. BY	E.J.CHRISTIAN
DATE	10/12/06

A-C MOTOR PERFORMANCE CURVES

A36WG1194-R013

ISSUE DATE 01/13/21

C/R 312091

Printed on 1/13/21 9:25 @ bengap01.bal

DUTY MASTER ALTERNATING CURRENT MOTORS

617428-348


ENCLOSURE: TOTALLY ENCLOSED


SQUIRREL-CAGE INDUCTION


MOUNTING: FOOT, F-1 SIDE


E365TC/E364TC MOUNTING HOLES

COOLING: FAN COOLED









SHEET NUMBER 1 OF 1

617428-348

FACE & ECCENTRICITY RUNOUT = .007 T.I.R. MAX.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: FROM AN AH OF 3.50 TO AN AH OF 5.62			
REV: A	VERSION: 01	REVISED: 08:21:20 03/21/2018	TDR: 000001065046
MODEL NO. 617428-348			
BY: USJEDIL		C	


BALDOR


E365/364TC TEFC FOOT F1/C1 CONDUIT BOX/SLINGERS/GROUND TAP

617428-348

416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED





(N. P. 1575-B)

416820-002

REV. DESC: ADJUST TEXT DARKNESS		
REV. LTR: B	VERSION: 02	TDR: 000001285318
FILE: \RAG\00022\453	REVISED: 09:36:26 09/24/2026	BY: USJOSUL
MTL: –		

ABB

CONN DIAG – STANDARD 9 LEAD, DELTA-CONNECTED

SH1 of 1