ABB BALDOR RELIANCE

Customer information packet

CEWDM3713T

15HP, 3495RPM, 3PH, 60HZ, 215TC, 3744M, TEFC, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/3/2026 6:10:01 AM

Specifications

Enclosure	TEFC
Frame	215TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM
	CURUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	17.700 A @ 460.0 V
	35.500 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	17.7 a
Insulation Class	F

Part Detail

Revision	C
Type	AC
Mech. spec.	37G815
Base	
Status	PRD/A
Elec. spec.	37WGZ713
Layout	37LYG815
Eff. date	08-31-2026
CD Diagram	CD0180
Poles	02
Leads	9#14
Proprietary	False
Created date	11-10-2025

Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3744M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	19.76 IN
Power Factor	86
Product Family	Wash Down
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3495 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L								
CAT.NO.	CEWDM3713T							
SPEC.	37G815Z713							
HP	15							
VOLTS	230/460							
AMP	35.5/17.7							
RPM	3495							
FRAME	215TC	**HZ**	60			**PH**	3	
SER.F.	1.15	**CODE**	J	**DES**	A	**CLASS**	F	
NEMA-NOM-EFF	91	**PF**	86					
RATING	40C AMB-CONT							
CC	010A							
DE	6307	**ODE**	6206					
ENCL	TEFC	**SN**						
BLANK	10:1CT, 20:1VT, 1.00SF							

AC Induction Motor Performance Data
Record # 116703
Typical performance - not guaranteed values

Winding: 37WGZ713-R002	**Type:** 3744M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			15	**Full Load Torque**	22.44 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			35.5/17.7	**Breakdown Torque**	119 LB-FT
R.P.M.			3495	**Pull-up Torque**	38 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	54.1 LB-FT
NEMA Design Code	A	**KVA Code**	J	**Starting Current**	146 A
Service Factor (S.F.)			1.15	**No-load Current**	6.2 A
NEMA Nom. Eff.	91	**Power Factor**	86	**Line-line Res. @ 25ºC**	0.53818 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	87°C
S.F. Amps			40.4/20.2	**Temp. Rise @ S.F. Load**	114°C
				Locked-rotor Power Factor	32.1
				Rotor inertia	0.401 lb-ft²

Load Characteristics 460 V, 60 Hz, 15 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	54	75	84	88	90	90	89
Efficiency	87.7	91.6	92.1	91.6	90.6	89.3	91
Speed	3575.5	3553	3529.7	3502.4	3472.3	3441.9	3484
Line amperes	7.4	10.1	13.5	17.4	21.6	26.1	19.9


ABB Motors and Mechanical Inc.


WINDING # 37WGZ713

15 HP 3 PH 60 HZ 3495 RPM 460 V 3744M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=119 PU=38 LR=54.1 LRA=146




37LYG815
717-735 = 18.63
736-744 = 19.76
745-750 = 20.51
751-756 = 21.26
5.01
.25
3.12
Ø10.28
NAMEPLATE
.31 KEY
2.38 LONG
Ø8.500
8.497
Ø9.05
Ø1.3750
1.3745
FORSHEDA
SLINGER
FORSHEDA
SLINGER
6 HOLES
Ø.43
4 HOLES
3 W/PLUGS
(EA. END)
5.50
.50
7.00
4.25
8.00
Ø9.55
7.93
2.26
45°
45°
10.02
5.25
5.19
LEAD
HOLE
.75 N.P.T.
4 HOLES
.50-13 TAP
ON
Ø7.25 B.C.
4.25
4.25
6.72
4.75
9.50
OMIT LOCK-WASHER &
APPLY SEALER UNDER
BEARING RETAINER SCREW
HEADS & HOUSING O.D.
BEFORE PRESSING IN SEAL
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERSION OF ACAD TO SWD INOPC PKG 19
REV: F
VERSION: 04
REVISED: 10:37:23 10/11/2022
TDR: 000001197758
MODEL NO. 37LYG815
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
STD HORZ 213-5TC 37M WD S/P #9 W/EPACT SHOVE
37LYG815

CD0180





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1