

ABB BALDOR RELIANCE III

Customer information packet

CEWDM4100T

15HP, 1180RPM, 3PH, 60HZ, 284TC, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	284TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	38.800 A @ 230.0 V 19.400 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	19.4 a

Part Detail

Revision	H
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	10WGZ490
Layout	10LYP093
Eff. date	02-21-2024
CD Diagram	CD0180
Poles	06
Leads	9#12
Proprietary	False
Created date	08-19-2019

Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	IP55
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1054M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	27.56 IN
Power Factor	77
Product Family	Washdown Features
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1180 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L									
CAT.NO.	CEWDM4100T								
SPEC.	10-0000-1009								
HP	15								
VOLTS	230/460 10:1CT/VT								
AMP	38.8/19.4								
RPM	1180								
FRAME	284TC		HZ	60			PH	3	
SER.F.	1.00	CODE	G	DES	B	CLASS	F		
NEMA-NOM-EFF	91.7	PF	77						
RATING	40C AMB-CONT								
CC	010A								
DE	6311		ODE	6309					
ENCL	TEFC	SN							
BLANK	1.15SF ON SINEWAVE								

AC Induction Motor Performance Data

Record # 74186

Typical performance - not guaranteed values

Winding: 10WGZ490-R006			Type: 1054M		Enclosure: TEFC		
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		15		Full Load Torque		66.4 LB-FT	
Volts		230/460		Start Configuration		direct on line	
Full Load Amps		38.8/19.4		Breakdown Torque		177 LB-FT	
R.P.M.		1180		Pull-up Torque		72.2 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		104 LB-FT	
NEMA Design Code		B	KVA Code	G	Starting Current		115 A
Service Factor (S.F.)		1		No-load Current		8.55 A	
NEMA Nom. Eff.		91.7	Power Factor	77	Line-line Res. @ 25°C		0.608 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		46°C	
S.F. Amps				Temp. Rise @ S.F. Load		57°C	
				Locked-rotor Power Factor		31.9	
				Rotor inertia		6.61 LB-FT2	

Load Characteristics 460 V, 60 Hz, 15 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	42	63	73	78	81	81
Efficiency	87.2	91.7	92.5	92.2	91.6	90.5
Speed	1196	1191	1187	1182	1176	1170
Line amperes	9.65	12.1	15.5	19.4	23.7	28.8


ABB Motors and Mechanical Inc.

WINDING # 10WGZ490

Typical performance - not guaranteed values.



15 HP 3 PH 60 HZ 1180 RPM 460 V 1054M

TORQUES (LB-FT): PO=177 PU=72.2 LR=104 LRA=115





CD0180


 LOW VOLTAGE
(2D)

 HIGH VOLTAGE
(1D)

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007

REV. LTR: D

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\148

REVISED: 10: 25: 29 02/19/2019

BY: ENBRIRO

MTL: —


BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1