Customer information packet

CEWDM4312T

50HP, 1185RPM, 3PH, 60HZ, 365TC, A3668M, TEFC
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/16/2026 3:28:30 AM

Specifications

Enclosure	TEFC
Frame	365TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	124.000 A @ 230.0 V
	132.000 A @ 208.0 V
	62.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	62.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Motor Lead Quantity/Wire Size	3 @ 4 AWG

Part Detail

Revision	G
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG4262
Layout	617428-348
Eff. date	01-12-2023
CD Diagram	416820-002
Poles	06
Leads	3#4,6#6
Proprietary	False
Created date	10-03-2022

Motor Standards	NEMA
Motor Type	A3668M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	33.48 IN
Power Factor	81
Product Family	Washdown Features
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Service Factor	1.15
Shaft Diameter	2.374 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1185 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP2496L



NP2428L											
SPEC NO.	A36-8075-4262	**CAT.NO.**	CEWDM4312T					**FRAME**	365TC		
HP	50	**VOLTS**	230/460	**PHASE**	3	**DESIGN**	B	**TYPE**	P		
RPM	1185	**AMPS**	124/62	**HZ**	60	**AMB**	40	**SF**	1.15		
DRIVE END BEARING	65BC03JGG30A	**DUTY**	CONT	**INSUL.CLASS**	F						
OPP D.E. BEARING	65BC03JGG30A	**ENCL**	TEFC	**CODE**	G						
SER.NO.		**POWER FACTOR**	81	**NEMA-NOM-EFFICIENCY**	94.1						
	10:1 CT AND 10:1 VT ON VPWM			**MAX CORR KVAR**	15.8	**GUARANTEED EFFICIENCY**	93				
	INVERTER, 1.00SF			**NEMA NOM/CSA QUOTED EFF**							
	IP55							**MOTOR WEIGHT**	908		

S/O	FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS
	365HP	50	P	3/60	1185	230/460

AMPS	DUTY	AMB °C/ INSUL	S.F.	NEMA DESIGN	CODE LETTER	ENCLOSURE
124/61.9	CONT	40/F	1.15	B	G	TEFC

E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES. @25 °C OHMS (BETWEEN LINES)
-	418141089AE	---	---	.0290/.116

PERFORMANCE

LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY
NO LOAD	0	23.9	1200	5.00	0
1/4	12.5	28.4	1197	45.8	90.1
2/4	25.0	37.2	1194	67.2	93.6
3/4	37.5	48.7	1191	76.4	94.3
4/4	50.0	61.9	1188	80.3	94.2
5/4	62.5	76.1	1185	82.0	93.7

SPEED TORQUE


	RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES
LOCKED ROTOR	0	165	365	375
PULL UP	540	147	325	335
BREAKDOWN	1135	253	559	200
FULL LOAD	1188	100	221	61.9

AMPERES SHOWN FOR 460 VOLT CONNECTION. IF OTHER CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

TYPICAL DATA
NEMA NOM. EFF. 94.1 PCT

ABB	DRAWN BY: C.B.ATANGANE CHECKED BY: J. P. TSAO APPROVED BY: W. L. SMITH DATE: 11/12/25	AC MOTOR PERFORMANCE DATA	A36WG4262-R001 DATE ISSUED 11/12/25

FRAME 365HP	RPM 1185	S.F. 1.15	ROTOR 418141089AE
HP 50	VOLTS 230/460	NEMA DESIGN B	TEST S.O. TYPICAL DATA
TYPE P	AMPS 124/61.9	CODE LETTER G	TEST DATE ---
PHASE / HERTZ 3/60	DUTY CONT	ENCLOSURE TEFC	STATOR RES. @ 25°C .0290/.116
	AMB °C / INSUL 40/F	E/S -	OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 230/460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

ABB	DRAWN BY: C.B.ATANGANE CHECKED BY: J. P. TSAO APPROVED BY: W. L. SMITH DATE: 11/12/25	AC MOTOR PERFORMANCE DATA	A36WG4262-R001 ISSUE DATE 11/12/25

DUTY MASTER ALTERNATING CURRENT MOTORS

617428-348


ENCLOSURE: TOTALLY ENCLOSED


SQUIRREL-CAGE INDUCTION


MOUNTING: FOOT, F-1 SIDE


E365TC/E364TC MOUNTING HOLES

COOLING: FAN COOLED









SHEET NUMBER 1 OF 1

617428-348

FACE & ECCENTRICITY RUNOUT = .007 T.I.R. MAX.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: FROM AN AH OF 3.50 TO AN AH OF 5.62			
REV: A	VERSION: 01	REVISED: 08:21:20 03/21/2018	TDR: 000001065046
MODEL NO. 617428-348			
BY: USJEDIL			C


BALDOR


E365/364TC TEFC FOOT F1/C1 CONDUIT BOX/SLINGERS/GROUND TAP

617428-348

416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED





(N. P. 1575-B)

REV. DESC: ADJUST TEXT DARKNESS		
REV. LTR: B	VERSION: 02	TDR: 000001285318
FILE: \RAG\00022\453	REVISED: 09:36:26 09/24/2026	BY: USJOSUL
MTL: –		

ABB

CONN DIAG – STANDARD 9 LEAD, DELTA-CONNECTED

SH1 of 1

416820-002