ABB BALDOR RELIANCE

Customer information packet

CEWDM4348T

40HP, 890RPM, 3PH, 60HZ, 365TC, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 10:16:20 PM

Specifications

Enclosure	TEFC
Frame	365TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	40.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	900 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	53.000 A @ 460.0 V
	106.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	53.0 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	IP55
KVA Code	G

Part Detail

Revision	A
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG0308
Layout	617428-348
Eff. date	09-13-2021
CD Diagram	416820-002
Poles	08
Leads	3#6,6#8
Proprietary	False
Created date	08-22-2019

Lifting Lugs	Standard Lifting Lugs
Motor Lead Quantity/Wire Size	3 @ 6 AWG
Motor Standards	NEMA
Motor Type	A36062M
Mounting Arrangement	F1
Number of Poles	8
Overall Length	33.48 IN
Power Factor	77
Product Family	Washdown Features
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Service Factor	1.15
Shaft Diameter	2.374 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	890 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP2496L
MOBIL POLYREX EM

NP2428L												
SPEC NO.	A36-6685-0308	**CAT.NO.**	CEWDM4348T						**FRAME**	365TC		
HP	40	**VOLTS**	230/460	**PHASE**	3	**DESIGN**	B	**TYPE**	P			
RPM	890	**AMPS**	106/53	**HZ**	60	**AMB**	40	**SF**	1.15			
DRIVE END BEARING	65BC03JGG30A	**DUTY**	CONT	**INSUL.CLASS**	F							
OPP D.E. BEARING	65BC03JGG30A	**ENCL**	TEFC	**CODE**	G							
SER.NO.		**POWER FACTOR**	77	**NEMA-NOM-EFFICIENCY**	91.7							
		MAX CORR KVAR	15	**GUARANTEED EFFICIENCY**	90.2							
	IP55	**NEMA NOM/CSA QUOTED EFF**										
	10:1CT AND 10:1VT ON VPWM INVE	RTER, 1.00SF	**MOTOR WEIGHT**	920								

REL. S.O.	FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS
	365TC	40	P	3/60	890	230/460

AMPS	DUTY	AMB °C/ INSUL.	S.F.	NEMA DESIGN	CODE LETTER	ENCL.
106/53	CONT	40/F	1.15	B	G	TEFC

E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES.@25 °C OHMS (BETWEEN LINES)
492342	418141073EE	---	---	.0486/.194

PERFORMANCE

LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY
NO LOAD	0	25.7	900	5.13	0
1/4	10.0	28.3	897	38.2	86.8
2/4	20.0	34.3	895	59.7	91.5
3/4	30.0	42.9	892	70.8	92.4
4/4	40.0	53.0	888	76.6	92.2
5/4	50.0	64.6	885	79.1	91.5

SPEED TORQUE

	RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES
LOCKED ROTOR	0	140	330	282
PULL UP	225	122	289	265
BREAKDOWN	845	224	529	157
FULL LOAD	888	100	236	53.0

AMPERES SHOWN FOR 460. VOLT CONNECTION. IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE


REMARKS: TYPICAL DATA
XE MOTOR-TYPICAL DATA-NEMA NOM. EFF. 91.7%

BALDOR
A MEMBER OF THE ABB GROUP

DR. BY C.E. JAMISON
CK. BY W.L. SMITH
APP. BY C.E. JAMISON
DATE 01/19/18

A-C MOTOR PERFORMANCE DATA A36WG0308-R005
ISSUE DATE 08/22/19

REL S.O.	RPM 890	S.F. 1.15	ROTOR 418141073EE
FRAME 365TC	VOLTS 230/460	NEMA DESIGN B	TEST S.O. TYPICAL DATA
HP 40	AMPS 106/53	CODE LETTER G	TEST DATE ---
TYPE P	DUTY CONT	ENCLOSURE TEFC	STATOR RES.@ 25 °C .0486/.194
PHASE/HERTZ 3/60	AMB °C/INSUL 40/F	E/S 492342	OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

BALDOR
A MEMBER OF THE ABB GROUP


DR. BY	C.E. JAMISON
CK. BY	W.L. SMITH
APP. BY	C.E. JAMISON
DATE	01/19/18

A-C MOTOR PERFORMANCE CURVES

A36WG0308-R005

ISSUE DATE 08/22/19

REL. S.O.	RPM 890	S.F. 1.15	ROTOR 418141073EE
FRAME 365TC	VOLTS 230/460	NEMA DESIGN B	TEST S.O. TYPICAL DATA
HP 40	AMPS 106/53	CODE LETTER G	TEST DATE ---
TYPE P	DUTY CONT	ENCLOSURE TEFC	STATOR RES.@ 25 ℃.0486/.194
PHASE/HERTZ 3/60	AMB ℃/INSUL 40/F	E/S 492342	OHMS (BETWEEN LINES)



THERMAL LIMIT CURVE

REMARKS: XE MOTOR-TYPICAL DATA-NEMA NOM. EFF. 91.7%

AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

DUTY MASTER ALTERNATING CURRENT MOTORS

617428-348


ENCLOSURE: TOTALLY ENCLOSED


SQUIRREL-CAGE INDUCTION


MOUNTING: FOOT, F-1 SIDE


E365TC/E364TC MOUNTING HOLES

COOLING: FAN COOLED









SHEET NUMBER 1 OF 1

617428-348

FACE & ECCENTRICITY RUNOUT = .007 T.I.R. MAX.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: FROM AN AH OF 3.50 TO AN AH OF 5.62			
REV: A	VERSION: 01	REVISED: 08:21:20 03/21/2018	TDR: 000001065046
MODEL NO. 617428-348			
BY: USJEDIL		C	


BALDOR


E365/364TC TEFC FOOT F1/C1 CONDUIT BOX/SLINGERS/GROUND TAP

617428-348

416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED





(N. P. 1575-B)

REV. DESC: ADJUST TEXT DARKNESS		
REV. LTR: B	VERSION: 02	TDR: 000001285318
FILE: \RAG\00022\453	REVISED: 09:36:26 09/24/2026	BY: USJOSUL
MTL: -		

ABB

CONN DIAG - STANDARD 9 LEAD, DELTA-CONNECTED

SH1 of 1

416820-002