ABB BALDOR RELIANCE

Customer information packet

CEWDM4314T

60HP, 1780RPM, 3PH, 60HZ, 364TC, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 8:44:14 AM

Specifications

Enclosure	TEFC
Frame	364TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	60.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	140.000 A @ 230.0 V
	152.000 A @ 208.0 V
	70.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.0 %
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	70.0 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	IP55

Part Detail

Revision	E
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG4075
Layout	617428-348
Eff. date	02-13-2025
CD Diagram	416820-002
Poles	04
Leads	3#4,6#6
Proprietary	False
Created date	08-23-2019

KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A3658M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	33.48 IN
Power Factor	84
Product Family	Washdown Features
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Service Factor	1.15
Shaft Diameter	2.374 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1780 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP2496L
MOBIL POLYREX EM

NP2428L										
SPEC NO.	A36-6179-4075	**CAT.NO.**	CEWDM4314T					**FRAME**	364TC	
HP	60	**VOLTS**	230/460	**PHASE**	3	**DESIGN**	B	**TYPE**	P	
RPM	1780	**AMPS**	140/70	**HZ**	60	**AMB**	40	**SF**	1.15	
DRIVE END BEARING	65BC03JGG30A	**DUTY**	CONT			**INSUL.CLASS**	F			
OPP D.E. BEARING	65BC03JGG30A	**ENCL**	TEFC	**CODE**	G					
SER.NO.		**POWER FACTOR**	84					**NEMA-NOM-EFFICIENCY**	95	
						MAX CORR KVAR	15	**GUARANTEED EFFICIENCY**	94.1	
	IP55					**NEMA NOM/CSA QUOTED EFF**				
	10:1CT AND 10:1VT ON VPWM INVE			RTER, 1.00SF				**MOTOR WEIGHT**		

AC Induction motor performance data

Record #72794 - Typical performance - not guaranteed values

Winding	A36WG4075
Type	A3658M
Enclosure	TEFC

Nameplate data			
Rated Output			60
Volts			230/460
Full Load Amps			140/70
R.P.M.			1780
Hz	60	Phase	3
KVA Code			G
S.F.			1.15
NEMA Nom. Eff.	95	Power Factor	84
Duty			CONT
S.F. Amps			

460 V, 60 Hz:

High Voltage Connection	
Full Load Torque	176.4 LB-FT
Start Configuration	direct on line
Breakdown Torque	422 LB-FT
Pull-up Torque	276 LB-FT
Locked-rotor Torque	352 LB-FT
Starting Current	462 A
No-load Current	24.8
Line-line Res. @ 25°C	0.10816 Ω
Temp. Rise @ Rated Load	56°C
Temp. Rise @ S.F. Load	70°C
Locked-rotor Power Factor	32.3
Rotor inertia	0

Load Characteristics 460 V, 60 Hz, 60 HP

% of Rated Load	NL	25	50	75	100	125	150	SF
Power Factor	4	51	73	81	84	86	85	85
Efficiency	0	92.6	95.1	95.4	95.2	94.6	93.8	94.8
Speed	1798.9	1796.4	1792.4	1788	1783.7	1778.3	1772.3	1780
Line amperes	24.8	29.7	40.7	54.4	69.7	86.6	105	79.8

ABB BALDOR RELIANCE

CUSTOMER INFORMATION PACKET


CEWDM4314T - 60HP, 1780RPM, 3PH, 60HZ, 364TC, TEFC, F1

WINDING # A36WG4075

REVIEW

60 HP 3 PH 60 HZ 1780 RPM 460 V A3658M

TORQUES (LB-FT): PO=422.00 PU=276.00 LR=352.00 LRA=462.00



USBRRAN1 5/4/2021 ACPERF, record # 72794

DUTY MASTER ALTERNATING CURRENT MOTORS

617428-348


ENCLOSURE: TOTALLY ENCLOSED


SQUIRREL-CAGE INDUCTION


MOUNTING: FOOT, F-1 SIDE


E365TC/E364TC MOUNTING HOLES

COOLING: FAN COOLED









SHEET NUMBER 1 OF 1

617428-348

FACE & ECCENTRICITY RUNOUT = .007 T.I.R. MAX.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: FROM AN AH OF 3.50 TO AN AH OF 5.62			
REV: A	VERSION: 01	REVISED: 08:21:20 03/21/2018	TDR: 000001065046
MODEL NO. 617428-348			
BY: USJEDIL			C


BALDOR


E365/364TC TEFC FOOT F1/C1 CONDUIT BOX/SLINGERS/GROUND TAP

617428-348

416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED





(N. P. 1575-B)

REV. DESC: ADJUST TEXT DARKNESS		
REV. LTR: B	VERSION: 02	TDR: 000001285318
FILE: \RAG\00022\453	REVISED: 09:36:26 09/24/2026	BY: USJOSUL
MTL: –		

ABB

CONN DIAG – STANDARD 9 LEAD, DELTA-CONNECTED

SH1 of 1

416820-002