ABB BALDOR RELIANCE

Customer information packet

CEWWDM23933T

15HP, 1765RPM, 3PH, 60HZ, 254TC, 3942M, TEFC, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/21/2026 5:15:30 AM

Specifications

Enclosure	TEFC
Frame	254TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM (OLD LOGO)
	CURUSEEV
	NEMA PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	36.000 A @ 230.0 V
	18.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	Z
Type	AC
Mech. spec.	39E490
Base	
Status	PRD/A
Elec. spec.	39WGW595
Layout	39LYE490
Eff. date	09-17-2024
CD Diagram	CD0005
Poles	04
Leads	9#12
Proprietary	False
Created date	11-21-2012

High Voltage Full Load Amps	18.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3942M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	23.57 IN
Power Factor	84
Product Family	Super White Washdown
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L									
CAT.NO.	CEWWDM23933T								
SPEC.	39E490W595G1								
HP	15								
VOLTS	230/460								
AMP	36/18								
RPM	1765								
FRAME	254TC	**HZ**	60			**PH**	3		
SER.F.	1.15	**CODE**	H	**DES**	A	**CLASS**	F		
NEMA-NOM-EFF	92.4	**PF**	84						
RATING	40C AMB-CONT								
CC	010A								
DE	6309	**ODE**	6309						
ENCL	TEFC	**SN**							
BLANK	-								


AC Induction Motor Performance Data
Record # 12820
Typical performance - not guaranteed values


Winding: 39WGW595-R001	**Type:** 3942M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			15	**Full Load Torque**	45 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			36/18	**Breakdown Torque**	143 LB-FT
R.P.M.			1765	**Pull-up Torque**	75 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	88 LB-FT
NEMA Design Code	B	**KVA Code**	H	**Starting Current**	125 A
Service Factor (S.F.)			1.15	**No-load Current**	6.95 A
NEMA Nom. Eff.	92.4	**Power Factor**	84	**Line-line Res. @ 25ºC**	0.577 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	60°C
S.F. Amps				**Temp. Rise @ S.F. Load**	72°C
				Locked-rotor Power Factor	33.3
				Rotor inertia	1.84 lb-ft²


Load Characteristics 460 V, 60 Hz, 15 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	49	71	81	86	88	89	87
Efficiency	87.9	92.1	93	92.8	92.3	91.5	92.5
Speed	1792	1784	1776	1766	1759	1750	1762
Line amperes	7.9	10.5	13.7	17.2	21	25	19.5


ABB Motors and Mechanical Inc.
WINDING # 39WGW595
15 HP 3 PH 60 HZ 1765 RPM 460 V 3942M
Typical performance - not guaranteed values.
TORQUES(LB-FT): PO=143 PU=75 LR=88 LRA=125
TORQUE
RPM
KW
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
KW
AMPS
PERCENT OF RATED OUTPUT (15 HP)
11/21/2026 ACPERF, record # 12820


39LYE490
(3924–3956) 23.57
6.41
3.75
.25
.38 KEY
2.88 LONG
8.500
8.497
1.625
1.624
9.44
PROTECH SEAL
(EA. END)
4 HOLES
3 W/PLUGS
EA. END
6 HOLES
ø.53
8.25
.63
10.00
4.75
11.25
12.43
9.73
6.49
3.37
45°
45°
12.00
6.25 +.00 −.06
.25
LEAD HOLE
1.25 N.P.T.
5.00
5.00
7.88
5.63
11.25
4 HOLES
.50–13 TAP
ON ø7.25 B.C.
PROTECH SEAL
WH4606A15
6309
FRONT END DETAIL
PROTECH SEAL
WH4606A15
6309
PULLEY END DETAIL
39LYE490
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.
REV. DESC: CHANGED LEADER NOTE
REV. LTR: C
VERSION: 03
TDR: 000000962273
FILE: \AAA\00196\412
REVISED: 10:56:07 01/20/2016
BY: ENNINDO
MTL: –
BALDOR
HORZ TEFC 254–6TC WD6 W/309 BRGS, PROTECH WD SEALS
SH 1 of 1

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS