

ABB BALDOR RELIANCE III

Customer information packet

CEWWDM3711T

10HP, 3490RPM, 3PH, 60HZ, 215TC, 3729M, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	215TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ 230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA EEV CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	11.800 A @ 460.0 V 23.600 A @ 230.0 V 24.900 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	90.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part Detail

Revision	P
Type	AC
Mech. spec.	37M881
Base	
Status	PRD/A
Elec. spec.	37WGS864
Layout	37LYM881
Eff. date	02-14-2024
CD Diagram	CD0005
Poles	02
Leads	9#14
Proprietary	False
Created date	12-14-2012

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	11.8 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3729M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	18.64 IN
Power Factor	87
Product Family	Super White Washdown
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3490 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L									
CAT.NO.	CEWWDM3711T								
SPEC.	37M881S864G1								
HP	10								
VOLTS	230/460								
AMP	23.2/11.6								
RPM	3490								
FRAME	215TC		HZ	60			PH	3	
SER.F.	1.15	CODE	G	DES	B	CLASS	F		
NEMA-NOM-EFF	90.2	PF	88						
RATING	40C AMB-CONT								
CC	010A								
DE	6307		ODE	6307					
ENCL	TEFC	SN							
BLANK									

AC Induction Motor Performance Data

Record # 35772

Typical performance - not guaranteed values

Winding: 37WGS864-R002			Type: 3730M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		10	Full Load Torque		15 LB-FT		
Volts		208-230/460	Start Configuration		direct on line		
Full Load Amps		24.9-23.6/11.8	Breakdown Torque		45.7 LB-FT		
R.P.M.		3490	Pull-up Torque		21.9 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		25.4 LB-FT	
NEMA Design Code		B	KVA Code	Starting Current		76.1 A	
Service Factor (S.F.)		1.15	No-load Current		4.12 A		
NEMA Nom. Eff.		90.2	Power Factor	Line-line Res. @ 25°C		0.991 Ω	
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		79°C
S.F. Amps					Temp. Rise @ S.F. Load		98°C
					Locked-rotor Power Factor		33.7
					Rotor inertia		0.255 LB-FT2

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	53	74	84	87	89	89	88
Efficiency	86.7	91	91.4	90.6	89.1	87.3	90
Speed	3575	3547	3516	3482	3445	3401	3464
Line amperes	4.94	6.85	9.1	11.8	14.7	18	13.5

ABB Motors and Mechanical Inc.

WINDING # 37WGS864

Typical performance - not guaranteed values.

10 HP 3 PH 60 HZ 3490 RPM 460 V 3730M

TORQUES (LB-FT) : PO=45.7 PU=21.9 LR=25.4 LRA=76.1





