

ABB BALDOR RELIANCE III

Customer information packet

CFSWDM23933T-E

15HP, 1765RPM, 3PH, 60HZ, 254TC, 3956M, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	254TC
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	17.500 A @ 460.0 V 35.000 A @ 230.0 V 38.000 A @ 208.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	AG
Type	AC
Mech. spec.	39E646
Base	
Status	PRD/A
Elec. spec.	39WGX682
Layout	39LYE646
Eff. date	02-10-2025
CD Diagram	CD0005
Poles	04
Leads	9#12
Proprietary	False
Created date	09-08-2016

High Voltage Full Load Amps	17.5 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3956M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	24.18 IN
Power Factor	86
Product Family	WD All SS Encapsulated
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP4427AAA01															
CAT #	CFSWDM23933T-E					WT	281		LBS						
SPEC	39E646X682G1					ENCL	TEFC								
SER #						CC	010A		IP	69					
HP	15		MAG CUR			14.2/7.1									
VOLTS	230/460					NEMA NOM. EFF					92.4				
AMPS	35/17.5					PF		86							
RATING	40C AMB-CONT														
RPM	1765					MAX RPM		2700							
FRAME	254TC	HZ		60		CODE	G		CLASS	H					
SER.F.	1.15	SF AMP					PH	3		DES	A				
DE	6309		ODE		6309										
LUBRICATION	POLYREX EM														
ID LOGO	INVERTER TYPE			VPWM		CHP	60		TO	90		1.5:1			
ID LOGO	WK2	2.44		CT	30		TO	60		2:1					
ID LOGO	SL HZ	1.2		VT	6		TO	60		10:1					
							QR								
YR															

