

ABB BALDOR RELIANCE III

Customer information packet

CFSWDM3554T-E

1.5HP, 1770RPM, 3PH, 60HZ, 145TC, 3526M, TEFC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	145TC
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA EEV CURUSEEV NEMA PREMIUM NEMA_PREMIUM WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.200 A @ 230.0 V 2.100 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part Detail

Revision	B
Type	AC
Mech. spec.	35E4743
Base	
Status	PRD/A
Elec. spec.	35WGZ819
Layout	35LYE4743
Eff. date	01-16-2025
CD Diagram	CD0005
Poles	04
Leads	9#18 Y
Proprietary	False
Created date	03-11-2022

Heater Indicator	No Heater
High Voltage Full Load Amps	2.1 a
Insulation Class	H
Inverter Code	Inverter Duty
KVA Code	M
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Finish	UNPAINTED
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3526M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.03 IN
Power Factor	76
Product Family	WD All SS Encapsulated
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP4427AAA01														
CAT #	CFSWDM3554T-E					WT	41		LBS					
SPEC	35E4743Z819G1					ENCL	TEFC							
SER #						CC	010A		IP	69				
HP	1.5					MAG CUR	2.5/1.25							
VOLTS	230/460					NEMA NOM. EFF					86.5			
AMPS	4.2/2.1					PF			76					
RATING	40C AMB-CONT													
RPM	1770					MAX RPM			2700					
FRAME	145TC		HZ	60		CODE	M		CLASS	H				
SER.F.	1.15	SF AMP	4.7/2.35				PH	3	DES	B				
DE	6205			ODE	6205									
LUBRICATION	POLYREX EM													
ID LOGO	INVERTER TYPE				VPWM		CHP	60		TO	90		1.5:1	
ID LOGO	WK2	0.189	CT	15	TO	60	4:1							
ID LOGO	SL HZ	1	VT	3	TO	60	20:1							
							QR							
YR														

AC Induction Motor Performance Data

Record # 87353

Preliminary Data Sheet

Winding: 35WGZ819-R001			Type: 3526M		Enclosure: TEFC		
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		1.5		Full Load Torque		4.47 LB-FT	
Volts		230/460		Start Configuration		direct on line	
Full Load Amps		4.2/2.1		Breakdown Torque		18.92 LB-FT	
R.P.M.		1770		Pull-up Torque		9.99 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		12.27 LB-FT	
NEMA Design Code		B	KVA Code	M	Starting Current		19.68 A
Service Factor (S.F.)		1.15		No-load Current		1.24 A	
NEMA Nom. Eff.		86.5	Power Factor	76	Line-line Res. @ 25°C		11.5 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		37°C	
S.F. Amps		4.7/2.35		Temp. Rise @ S.F. Load		44°C	
				Locked-rotor Power Factor		59.3	
				Rotor inertia		0.188 lb-ft²	

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	36	55	68	76	81	84	79
Efficiency	77.4	85.3	87.5	87.7	87.2	86	87.4
Speed	1793	1786	1780	1772	1765	1756	1768
Line amperes	1.32	1.5	1.78	2.11	2.49	2.92	2.34


ABB Motors and Mechanical Inc.

WINDING # 35WGZ819


Typical performance - not guaranteed values.

1.5 HP 3 PH 60 HZ 1770 RPM 460 V 3526M

TORQUES (LB-FT): PO=18.92 PU=9.99 LR=12.27 LRA=19.68



35LYE4743



REV. DESC: REMOVE FACE DRAINS & DRAIN FTG; ADD DRAIN PLUG			
REV: D	VERSION: 04	REVISED: 10:50:10 01/27/2023	TDR: 000001202627
35LYE4743		MODEL NO. 35LYE4743	REF: -
		BY: ENSTEK0	

BALDOR

STD HORZ 143-5TC TEFC 35M WD11/12

35LYE4743

