

BALDOR • RELIANCE

Customer information packet

CFSWDM3559-E-G

3/2.2KW 4:1CT, 10:1VTHP, 3470 1/MIN IP69K

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CE CSA EEV NEMA PREMIUM NEMA_PREMIUM WEEE UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	7.700 A @ 208.0 V 7.200 A @ 230.0 V 3.600 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated

Part detail

Revision	F
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	35WGR930
Layout	35LY-000-653
Eff. date	05-12-2023
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	10-05-2021

Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	3.6 a
Insulation Class	H
Inverter Code	Inverter Duty
KVA Code	P
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Finish	UNPAINTED
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3546M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	16.21 IN
Power Factor	90
Product Family	WD All SS Encapsulated
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	3470 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4294A01										
CAT.NO.	CFSWDM3559-E-G									
SPEC.	35-0000-1317									
HP	3/2.2KW 4:1CT,10:1VT						IP	69		
VOLTS	230/460									
AMPS	7.2/3.6									
R.P.M.	3470 1/MIN IC411 29KG									
FRAME	56C		HZ	60		PH	3			
SER.F.	1.15	CODE	P	DES.	A	CLASS	H			
NEMA NOM. EFF.	86.5	P.F.	90							
RATING	40C AMB-S1 CONT				WT.					
CC	010A	USABLE AT 208V				N/A				
DE	6205	ODE	6205							
ENCL	TEFC	SN								
IE3-87.2(75%)86.3(50%)										

AC Induction Motor Performance Data

Record # 55293

Typical performance - not guaranteed values

Winding: 35WGR930-R011		Type: 3546M		Enclosure: TEFC	
Nameplate Data			460 V, 60 Hz: High Voltage Connection		
Rated Output (HP)		3	Full Load Torque		4.5 LB-FT
Volts		230/460	Start Configuration		direct on line
Full Load Amps		7.2/3.6	Breakdown Torque		17.2 LB-FT
R.P.M.		3470	Pull-up Torque		10.5 LB-FT
Hz	60 Phase	3	Locked-rotor Torque		17 LB-FT
NEMA Design Code	A KVA Code	P	Starting Current		48.3 A
Service Factor (S.F.)		1.15	No-load Current		1.25 A
NEMA Nom. Eff.	86.5 Power Factor	90	Line-line Res. @ 25°C		3.47 Ω
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		63°C
S.F. Amps			Temp. Rise @ S.F. Load		74°C
			Locked-rotor Power Factor		42.3
			Rotor inertia		0.127 LB-FT ²

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	59	79	87	90	91	90	91
Efficiency	80.1	86.4	87.3	86.9	85.7	83.9	86.2
Speed	3567	3541	3510	3479	3443	3403	3457
Line amperes	1.53	2.07	2.78	3.55	4.42	5.4	4.07


ABB Motors and Mechanical Inc.

WINDING # 35WGR930


3 HP 3 PH 60 HZ 3470 RPM 460 V 3546M

Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=17.2 PU=10.5 LR=17 LRA=48.3




9/9/2024 ACPERF, record # 55293



CD0005




LOW VOLTAGE
(2Y)



LINE

HIGH VOLTAGE
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS