

ABB BALDOR RELIANCE III

Customer information packet

CFSWDNM3558T-E-G

2HP, 1760RPM, 3PH, 60HZ, 145TC, 3546M, TENV, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TENV
Frame	145TC
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CURUSEEV NEMA PREMIUM WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	5.300 A @ 230.0 V 5.600 A @ 208.0 V 2.650 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	B
Type	AC
Mech. spec.	35E6049
Base	
Status	PRD/A
Elec. spec.	35WGZ811
Layout	35LYE6049
Eff. date	01-29-2026
CD Diagram	CD0005
Poles	04
Leads	9#18 Y
Proprietary	False
Created date	02-23-2023

High Voltage Full Load Amps	2.7 a
Insulation Class	H
Inverter Code	Inverter Duty
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Finish	UNPAINTED
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3546M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.84 IN
Power Factor	80
Product Family	WD All SS Encapsulated
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

	NP4427AAA01A								
CAT #	CFSWDNM3558T-E-G				WGT		LBS		
SPEC	35E6049Z811G1				ENCL	TENV			
SER #					CC	O10A	IP	69	
HP	2	MAG CUR			2.7/1.35				
VOLTS	230/460				NEMA NOM.	EFF		86.5	
AMPS	5.3/2.65					PF	80		
RATING	40C AMB-CONT								
RPM	1760				MAX RPM	2700			
FRAME	145TC	HZ	60	CODE	L	CLASS	H		
SER.F.	1.15	SF AMP	6/3	PH		3	DES	B	
DE	6205		ODE	6205					
LUBRICATION	POLYREX EM								
ID LOGO	INVERTER TYPE		VPWM		CHP	60	TO	90	1.5:1
ID LOGO	WK2	0.332	CT	3	TO	60	20:1		
ID LOGO	SL HZ	1.33	VT	3	TO	60	20:1		
						QR			
YR									

AC Induction Motor Performance Data

Record # 87105

Preliminary Data Sheet

Winding: 35WGZ811-R001			Type: 3546M		Enclosure: TENV	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		2	Full Load Torque		6 LB-FT	
Volts		230/460	Start Configuration		direct on line	
Full Load Amps		5.3/2.65	Breakdown Torque		27.78 LB-FT	
R.P.M.		1760	Pull-up Torque		16.81 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		21.79 LB-FT
NEMA Design Code		B	KVA Code		L	Starting Current
Service Factor (S.F.)		1.15	No-load Current		1.36 A	
NEMA Nom. Eff.		86.5	Power Factor		80	Line-line Res. @ 25°C
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load	
S.F. Amps		6/3	Temp. Rise @ S.F. Load		122°C	
			Locked-rotor Power Factor		51.7	
			Rotor inertia		0.332 lb-ft²	

Load Characteristics 460 V, 60 Hz, 2 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	39	61	73	80	85	87	83
Efficiency	83.3	88.6	89.2	88.7	87.5	86	88
Speed	1790	1781	1771	1760	1748	1735	1753
Line amperes	1.5	1.78	2.17	2.65	3.18	3.77	2.97

ABB Motors and Mechanical Inc.

WINDING # 35WGZ811

Typical performance - not guaranteed values.

2 HP 3 PH 60 HZ 1760 RPM 460 V 3546M

TORQUES (LB-FT) : PO=27.78 PU=16.81 LR=21.79 LRA=25.07





