

ABB BALDOR RELIANCE III

Customer information packet

CHM365A

.5HP, 1140RPM, 3PH, 60HZ, 56YZ, 3418M, TEAO, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEAO
Frame	56YZ
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Resilient
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.200 A @ 460.0 V 2.400 A @ 230.0 V 2.700 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	72.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Resilient Mount
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	M
Type	AC
Mech. spec.	34M249
Base	
Status	PRD/A
Elec. spec.	34WGW529
Layout	34LYM249
Eff. date	10-28-2024
CD Diagram	CD0007
Poles	06
Leads	12#18
Proprietary	False
Created date	05-24-2013

High Voltage Full Load Amps	1.2 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Terminal Panel Or Lead Hole
Motor Lead Quantity/Wire Size	12 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3418M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	12.70 IN
Power Factor	55
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Resilient Mount
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1140 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload

Winding Thermal 1 Location

SB

Nameplate

NP1257L											
CAT.NO.	CHM365A										
SPEC.	34M249W529G1										
HP	.5										
VOLTS	230/460										
AMP	2.4/1.2										
RPM	1140										
FRAME	56YZ				HZ		60		PH		3
SER.F.	1.25	CODE	J	DES		B	CL	B			
NEMA-NOM-EFF	72	PF	55								
RATING	40C AMB-CONT										
CC											
DE	6203	ODE		6203							
ENCL	TEAO	SN									
	SFA 2.6/1.3										

AC Induction Motor Performance Data

Record # 42100

Typical performance - not guaranteed values

Winding: 34WGW529-R006			Type: 3418M		Enclosure: TEAO	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		.5	Full Load Torque		2.3 LB-FT	
Volts		230/460	Start Configuration		direct on line	
Full Load Amps		2.4/1.2	Breakdown Torque		7.7 LB-FT	
R.P.M.		1140	Pull-up Torque		6 LB-FT	
Hz		60	Phase		3	
NEMA Design Code		B	KVA Code		J	
Service Factor (S.F.)		1.25	No-load Current		0.95 A	
NEMA Nom. Eff.		72	Power Factor		55	
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		
S.F. Amps		2.6/1.3		Temp. Rise @ S.F. Load		
				Locked-rotor Power Factor		
				Rotor inertia		
				0.0428 LB-FT2		

Load Characteristics 460 V, 60 Hz, 0.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	20	34	45	55	62	68	62
Efficiency	48	63	67	72	72	71	72
Speed	1185	1170	1155	1140	1120	1100	1120
Line amperes	0.95	1	1.1	1.2	1.3	1.5	1.3


ABB Motors and Mechanical Inc.

WINDING # 34WGW529



Typical performance - not guaranteed values.

0.5 HP 3 PH 60 HZ 1140 RPM 460 V 3418M

TORQUES (LB-FT) : PO=7.7 PU=6 LR=6.2 LRA=5



CD0007



- NOTES:
1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 2. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
 3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0007

REV. DESC: ADDED "CK" PLANT CODE			
REV. LTR: E	BY: EAH	REVISED: 05/06/99 17:1	TDR: 0181040
200000		FILE: AAA00008370	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, THERMAL, 12 LEADS