

ABB BALDOR RELIANCE III

Customer information packet

CFSWDM41903T

25HP, 1775RPM, 3PH, 60HZ, 284TC, 4068M, TEFC, F

Specifications

Enclosure	TEFC
Frame	284TC
Frame Material	Stainless Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	25.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA NEMA PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	30.000 A @ 460.0 V 60.000 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.6 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	30.0 a
Insulation Class	H

Part Detail

Revision	K
Type	AC
Mech. spec.	40E429
Base	
Status	PRD/A
Elec. spec.	40WGX292
Layout	40LYE429
Eff. date	09-22-2023
CD Diagram	CD0180
Poles	04
Leads	9#10
Proprietary	False
Created date	01-10-2018

Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4068M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	28.14 IN
Power Factor	84
Product Family	WD All SD Non-Encapsulated
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

NP4427AAA05												
CAT #	CFSWDM41903T					LBS						
SPEC	40E429X292G1					ENCL	TEFC					
SER #						CC	010A	IP	69			
HP	25		MAG CUR			24/12						
VOLTS	230/460					NEMA NOM. EFF		93.6				
AMPS	60/30					PF	84					
RATING	40C AMB-CONT											
RPM	1775					MAX RPM		2700				
FRAME	284TC	HZ	60		CODE	H	CLASS	H				
SER.F.	1.15	SF AMP						PH	3	DES	A	
DE	6311		ODE		6311							
LUBRICATION	POLYREX EM											
ID LOGO	VPWM	CHP	60	TO	90	1.5:1						
ID LOGO	WK2	5.41	CT	12	TO	60	5:1					
ID LOGO	SL HZ	0.8	VT	6	TO	60	10:1					
	QR											
YR												

AC Induction Motor Performance Data

Record # 70431

Typical performance - not guaranteed values

Winding: 40WGX292-R001			Type: 4068M		Enclosure: TEFC		
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		25	Full Load Torque		73.77 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		60/30	Breakdown Torque		253 LB-FT		
R.P.M.		1775	Pull-up Torque		114 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		149 LB-FT	
NEMA Design Code		A	KVA Code	H		Starting Current	211 A
Service Factor (S.F.)		1.15	No-load Current		12 A		
NEMA Nom. Eff.		93.6	Power Factor	84		Line-line Res. @ 25°C	0.24122 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		69°C
S.F. Amps			Temp. Rise @ S.F. Load		82°C		
			Locked-rotor Power Factor		30.2		

Load Characteristics 460 V, 60 Hz, 25 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	47	69	79	84	86	87	85
Efficiency	89.8	93.4	94.1	94.1	93.7	92.9	93.9
Speed	1794.2	1788.5	1782.1	1775.7	1769.6	1761.7	1772
Line amperes	13.9	18.1	23.5	29.6	36.3	43.6	33.6


ABB Motors and Mechanical Inc.

WINDING # 40WGX292


Typical performance - not guaranteed values.

25 HP 3 PH 60 HZ 1775 RPM 460 V 4068M


TORQUES (LB-FT): PO=253 PU=114 LR=149 LRA=211




CD0180



LOW VOLTAGE
(2D)



HIGH VOLTAGE
(1D)



NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007

REV. LTR: D

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\148

REVISED: 10: 25: 29 02/19/2019

BY: ENBRIRO

MTL: —



BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1