ABB BALDOR RELIANCE

Customer information packet

CHM465A

.75HP, 1140RPM, 3PH, 60HZ, 56YZ, 3428M, TEAO, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/13/2026 11:24:32 AM

Specifications

Enclosure	TEAO
Frame	56YZ
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
	208.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Resilient
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.300 A @ 208.0 V
	3.000 A @ 230.0 V
	1.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	77.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Resilient Mount
Front Shaft Indicator	None

Part Detail

Revision	L
Type	AC
Mech. spec.	34M249
Base	
Status	PRD/A
Elec. spec.	34WGY151
Layout	34LYM249
Eff. date	10-28-2024
CD Diagram	CD0007
Poles	06
Leads	12#18
Proprietary	False
Created date	05-30-2013

Heater Indicator	No Heater
High Voltage Full Load Amps	1.5 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Terminal Panel Or Lead Hole
Motor Lead Quantity/Wire Size	12 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3428M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	13.58 IN
Power Factor	59
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Resilient Mount
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1140 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	Automatic Thermal Overload
Winding Thermal 1 Location	EP

Nameplate

NP1257L											
CAT.NO.	CHM465A										
SPEC.	34M249Y151G1										
HP	.75										
VOLTS	208-230/460										
AMP	3.3-3/1.5										
RPM	1140										
FRAME	56YZ		**HZ**	60		**PH**	3				
SER.F.	1.15	**CODE**	K	**DES**	B	**CL**	B				
NEMA-NOM-EFF	77	**PF**	59								
RATING	40C AMB-CONT										
CC											
DE	6203	**ODE**	6203								
ENCL	TEAO	**SN**									

AC Induction Motor Performance Data
Record # 42368
Typical performance - not guaranteed values

Winding: 34WGY151-R004 **Type:** 3428M **Enclosure:** TEAO

Nameplate Data		
Rated Output (HP)		.75 AIR OVER
Volts		208-230/460
Full Load Amps		3.3-3/1.5
R.P.M.		1140
Hz	60 **Phase**	3
NEMA Design Code	B **KVA Code**	K
Service Factor (S.F.)		1.15
NEMA Nom. Eff.	77 **Power Factor**	59
Rating - Duty		40C AMB-CONT

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	3.4 LB-FT
Start Configuration	direct on line
Breakdown Torque	11.8 LB-FT
Pull-up Torque	9.3 LB-FT
Locked-rotor Torque	9.7 LB-FT
Starting Current	7.4 A
No-load Current	1.1 A
Line-line Res. @ 25ºC	21.9 Ω
Temp. Rise @ Rated Load	
Locked-rotor Power Factor	56
Rotor inertia	0.0665 LB-FT2

Load Characteristics 460 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	26	40	51	59	65	68	63
Efficiency	60	72	76	77	75	73	75.8
Speed	1185	1170	1155	1135	1115	1095	1123
Line amperes	1.1	1.2	1.4	1.5	1.7	2	1.62


ABB Motors and Mechanical Inc.

WINDING # 34WGY151


0.75 HP 3 PH 60 HZ 1140 RPM 460 V 3428M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=11.8 PU=9.3 LR=9.7 LRA=7.4




11/13/2026 ACPERF, record # 42368


34LYM249
5.84
4.09
GROUND SCREW
6.34
3.50 +.00 -.06
THERMAL (WHEN REQ'D)
4 SLOTS .34 WIDE
2.44
2.44
3.25
6.50
408-416 = 12.09
417-421 = 12.71
422-428 = 13.59
429-432 = 14.09
3.35
3.00
1.12
.88
.19 KEY
1.38 LONG
LEAD HOLE Ø.88 (W/PLUG)
NAMEPLATE
Ø.6250
.6245
GREEN GROUND LEAD
CORD SLOT W/PLUG
4 STUDS #8-32 THREAD ON Ø5.12 B.C.
3.00
2.75
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CHANGE CLAMP SCREW TO CORRECT WAY
REV: C
VERSION: 03
REVISED: 09:25:28 06/21/2023
TDR: 000001211422
MODEL NO. 34LYM249
REF: -
BY: ENFRAJ0
B
BALDOR - RELIANCE®
RESIL 34M NEMA 56YZ TEAO W/EXTENDED T-BOLTS ON 5.12 B.C.
SH 1 of 1
34LYM249

CD0007





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: ADDED "CK" PLANT CODE			BALDOR ELECTRIC Co.
REV. LTR: E	BY: EAH	REVISED: 05/06/99 17:1	TDR: 0181040
CD0007		FILE: AAA00008370	MDL: –
		MTL: –	3PH, DV, THERMAL, 12 LEADS

CD0007