

ABB BALDOR RELIANCE III

Customer information packet

CHC244A

.33HP, 1700RPM, 1PH, 60HZ, 48Z, 3414C, TEAO, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEAO
Frame	48Z
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Oil Capacitor Start and Run
Output @ Frequency	.330 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Resilient
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.700 A @ 230.0 V 3.400 A @ 115.0 V
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	70.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Resilient Mount
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.7 a
Insulation Class	B

Part Detail

Revision	N
Type	AC
Mech. spec.	34M212
Base	
Status	PRD/A
Elec. spec.	34WGR057
Layout	34LYM212
Eff. date	10-28-2024
CD Diagram	CD0804
Poles	04
Leads	7#18
Proprietary	False
Created date	05-14-2013

Inverter Code	Not Inverter
KVA Code	E
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Terminal Panel Or Lead Hole
Motor Lead Quantity/Wire Size	7 @ 18 AWG
Motor Lead Termination	None
Motor Standards	NEMA
Motor Type	3414C
Mounting Arrangement	F1
Number of Poles	4
Overall Length	11.35 IN
Power Factor	90
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Resilient Mount
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.500 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible: Connected Standard
Shaft Slinger Indicator	No Slinger
Speed	1700 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload
Winding Thermal 1 Location	WG

Nameplate

NP1257L											
CAT.NO.	CHC244A										
SPEC.	34M212R057G1										
HP	.33										
VOLTS	115/230										
AMP	3.4/1.7										
RPM	1700										
FRAME	48Z			HZ		60		PH		1	
SER.F.	1.15	CODE	E	DES	-	CL	B				
NEMA-NOM-EFF	70	PF	90								
RATING	40C AMB-CONT										
CC											
DE	6203		ODE		6203						
ENCL	TEAO	SN									

AC Induction Motor Performance Data

Record # 43035

Typical performance - not guaranteed values

Winding: 34WGR057-R001			Type: 3414C		Enclosure: TEAO	
Nameplate Data				230 V, 60 Hz: High Voltage Connection		
Rated Output (HP)		.33 AIR OVER		Full Load Torque		1.03 LB-FT
Volts		115/230		Start Configuration		direct on line
Full Load Amps		3.4/1.7		Breakdown Torque		2.54 LB-FT
R.P.M.		1700		Pull-up Torque		0.347 LB-FT
Hz	60	Phase	1	Locked-rotor Torque		0.437 LB-FT
NEMA Design Code		- KVA Code		Starting Current		6.99 A
Service Factor (S.F.)		1.15		No-load Current		0.856 A
NEMA Nom. Eff.		70	Power Factor	Line-line Res. @ 25°C		10.817 Ω A Ph 9.0175 Ω B Ph
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		

Load Characteristics 230 V, 60 Hz, 0.33 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	72	81	87	90	92	93	91
Efficiency	40.9	60	69.7	73.2	73	71.8	73.1
Speed	1781.1	1764.1	1747.9	1725	1697.9	1667.8	1709
Line amperes	0.975	1.15	1.36	1.66	1.98	2.35	1.85


ABB Motors and Mechanical Inc.


WINDING # 34WGR057

Typical performance - not guaranteed values.



0.33 HP 1 PH 60 HZ 1700 RPM 230 V 3414C

TORQUES (LB-FT) : PO=2.54 PU=0.347 LR=0.437 LRA=6.99





CD0804



- NOTES:
1. CONNECT LINE LEADS TO L1 AND L2.
LOW VOLTAGE: CONNECT AS SHOWN.
HIGH VOLTAGE: MOVE LEAD J TO TERM. 3.
MOVE LEAD 2 TO TERM. 4.
 2. CONNECTIONS ARE SHOWN FOR STANDARD ROTATION (CCW FACING END OPPOSITE SHAFT EXTENSION). INTERCHANGE LEADS 5 AND 8 TO REVERSE ROTATION.
 3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: OMIT (WHT/BLU) MARKER			
REV. LTR: E	BY: MEM	REVISED: 10:37:34 11/25/2002	TDR: 288036
FILE: AAA00007297		REF: CD0804	
MTL: -			

BALDOR ELECTRIC Co.

TYPE C, DV, REV, THERMAL (T*STAT IN LINE), TERM PLATE

CD0804