

ABB BALDOR RELIANCE III

Customer information packet

CHM465A

.75HP, 1140RPM, 3PH, 60HZ, 56YZ, 3428M, TEAO, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEAO
Frame	56YZ
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ 208.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Resilient
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.300 A @ 208.0 V 3.000 A @ 230.0 V 1.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	77.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Resilient Mount
Front Shaft Indicator	None

Part Detail

Revision	L
Type	AC
Mech. spec.	34M249
Base	
Status	PRD/A
Elec. spec.	34WGY151
Layout	34LYM249
Eff. date	10-28-2024
CD Diagram	CD0007
Poles	06
Leads	12#18
Proprietary	False
Created date	05-30-2013

Heater Indicator	No Heater
High Voltage Full Load Amps	1.5 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Terminal Panel Or Lead Hole
Motor Lead Quantity/Wire Size	12 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3428M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	13.58 IN
Power Factor	59
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Resilient Mount
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1140 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor



Winding Thermal 1

Automatic Thermal Overload

Winding Thermal 1 Location

EP

Nameplate

NP1257L											
CAT.NO.	CHM465A										
SPEC.	34M249Y151G1										
HP	.75										
VOLTS	208-230/460										
AMP	3.3-3/1.5										
RPM	1140										
FRAME	56YZ			HZ	60			PH	3		
SER.F.	1.15		CODE	K		DES	B	CL	B		
NEMA-NOM-EFF	77		PF	59							
RATING	40C AMB-CONT										
CC											
DE	6203		ODE	6203							
ENCL	TEAO		SN								

AC Induction Motor Performance Data

Record # 42368

Typical performance - not guaranteed values

Winding: 34WGY151-R004			Type: 3428M		Enclosure: TEAO	
Nameplate Data				460 V, 60 Hz: High Voltage Connection		
Rated Output (HP)		.75 AIR OVER		Full Load Torque		3.4 LB-FT
Volts		208-230/460		Start Configuration		direct on line
Full Load Amps		3.3-3/1.5		Breakdown Torque		11.8 LB-FT
R.P.M.		1140		Pull-up Torque		9.3 LB-FT
Hz	60	Phase	3	Locked-rotor Torque		9.7 LB-FT
NEMA Design Code		B	KVA Code	Starting Current		7.4 A
Service Factor (S.F.)		1.15		No-load Current		1.1 A
NEMA Nom. Eff.		77	Power Factor	Line-line Res. @ 25°C		21.9 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		
				Locked-rotor Power Factor		56
				Rotor inertia		0.0665 LB-FT2

Load Characteristics 460 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	26	40	51	59	65	68	63
Efficiency	60	72	76	77	75	73	75.8
Speed	1185	1170	1155	1135	1115	1095	1123
Line amperes	1.1	1.2	1.4	1.5	1.7	2	1.62


ABB Motors and Mechanical Inc.


WINDING # 34WGY151

Typical performance - not guaranteed values.



0.75 HP 3 PH 60 HZ 1140 RPM 460 V 3428M

TORQUES (LB-FT): PO=11.8 PU=9.3 LR=9.7 LRA=7.4





CD0007



- NOTES:
1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 2. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
 3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: ADDED "CK" PLANT CODE			
REV. LTR: E	BY: EAH	REVISED: 05/06/99 17:1	TDR: 0181040
L00000		FILE: AAA00008370	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, THERMAL, 12 LEADS

CD0007