

ABB BALDOR RELIANCE III

Customer information packet

CJWDM3463

.75HP, 3450RPM, 3PH, 60HZ, 56J, 3514M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56J
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ 230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.400 A @ 460.0 V 2.800 A @ 230.0 V 3.000 A @ 208.0 V 3.800 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	68.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part Detail

Revision	R
Type	AC
Mech. spec.	35E2234
Base	
Status	PRD/A
Elec. spec.	35WG0081
Layout	35LYE2234
Eff. date	09-11-2023
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	10-15-2013

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.4 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3514M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	12.72 IN
Power Factor	74
Product Family	Wash Down
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Ext Thread
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.50
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1496L									
CAT.NO.	CJWDM3463								
SPEC.	35E2234-0081G1								
HP	.75								
VOLTS	208-230/460								
AMP	3-2.8/1.4								
RPM	3450								
FRAME	56J		HZ		60		PH		3
SER.F.	1.50	CODE		L	DES	B	CLASS		F
NEMA-NOM-EFF	68	PF		74					
RATING	40C AMB-CONT								
CC									
DE	6205		ODE		6203				
ENCL	TEFC	SN							
	SFA 3.8-3.6/1.8								

AC Induction Motor Performance Data

Record # 78924

Typical performance - not guaranteed values

Winding: 35WG0081-R059			Type: 3514M		Enclosure: TEFC	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		.75	Full Load Torque		1.12 LB-FT	
Volts		208-230/460	Start Configuration		direct on line	
Full Load Amps		3-2.8/1.4	Breakdown Torque		4.98 LB-FT	
R.P.M.		3450	Pull-up Torque		3.71 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		4.4 LB-FT
NEMA Design Code		B	KVA Code	Starting Current		8.85 A
Service Factor (S.F.)		1.5		No-load Current		0.908 A
NEMA Nom. Eff.		68	Power Factor	Line-line Res. @ 25°C		18.6 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		43°C
S.F. Amps		3.8-3.6/1.8		Temp. Rise @ S.F. Load		57°C
			Locked-rotor Power Factor		67.5	
			Rotor inertia		0.0387 LB-FT2	

Load Characteristics 460 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	43	58	68	76	80	83	83
Efficiency	41.9	57.7	64.8	69.2	70.7	71.1	71.1
Speed	3559	3534	3507	3475	3441	3402	3402
Line amperes	0.98	1.05	1.18	1.31	1.51	1.71	1.71

ABB Motors and Mechanical Inc.

WINDING # 35WG0081

Typical performance - not guaranteed values.

0.75 HP 3 PH 60 HZ 3450 RPM 460 V 3514M

TORQUES (LB-FT) : PO=4.98 PU=3.71 LR=4.4 LRA=8.85





