

DUTY MASTER ALTERNATING CURRENT MOTORS





SQUIRREL-CAGE INDUCTION

ENCLOSURE: UL LISTED MOTOR

MOUNTING: FOOT, F-1 SIDE

G447T/G445T FRAME MOUNTING HOLES

COOLING: FAN COOLED



1 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

DIMENSIONS ARE IN INCHES.
WEIGHT (LBS): 2610, MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: NEW DRAWING			
REV: -	VERSION: 00	REVISED: 07:50:02 08/27/2018	TDR: 000001082879
MODEL NO. 617426-328		REF:	
BY: USJEDIL	Material:		

BALDOR

G447/445T XP F1 FOOT CI BOX W/ 4.00" NPT/TACONITE/AIR DEF