



---

# Customer information packet

## CSPM2506T

7.5HP, 1180RPM, 3PH, 60HZ, 254TC, 3950M, OPSB

Class - None

Division - Not Applicable

## Specifications

Enclosure	ODP
Frame	254TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CURUSEEV NEMA_PREMIUM WEEE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	22.000 A @ 230.0 V 26.000 A @ 208.0 V 11.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater

## Part detail


Revision	A
Type	AC
Mech. spec.	39E763
Base	
Status	PRD/A
Elec. spec.	39WGW951
Layout	39LYE763
Eff. date	11-18-2024
CD Diagram	CD0005
Poles	06
Leads	9#12
Proprietary	False
Created date	11-16-2023

High Voltage Full Load Amps	11.0 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Quantity/Wire Size	9 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3950M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	23.19 IN
Power Factor	70
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1180 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None


**Nameplate**

**NP4423A01A01L**


<b>CAT #</b>	CSPM2506T	<b>WGT</b>	248	<b>LBS</b>	
<b>SPEC</b>	39E763W951	<b>ENCL</b>	OPSB		
<b>SER #</b>		<b>CC</b>	010A	<b>IP</b>	23
<b>HP</b>	7.5	<b>MAG CUR</b>	11.4/5.7		
<b>VOLTS</b>	230/460	<b>NEMA NOM. EFF</b>		91.7	
<b>AMPS</b>	22/11	<b>PF</b>	70		
<b>RATING</b>	40C AMB-CONT				
<b>RPM</b>	1180	<b>MAX RPM</b>	1800		
<b>FRAME</b>	254TC	<b>HZ</b>	60	<b>CODE</b>	J
		<b>CLASS</b>		F	
<b>SER.F.</b>	1.15	<b>SF AMP</b>		<b>PH</b>	3
		<b>DES</b>		B	
<b>DE</b>	6309	<b>ODE</b>	6208		
<b>LUBRICATION</b>	POLYREX EM				
<b>ID LOGO</b>	<b>INVERTER TYPE</b>	<b>VPWM</b>	<b>CHP</b>	1.5	<b>TO</b>
				1	1.5:1
<b>ID LOGO</b>	<b>WK2</b>	4.02	<b>CT</b>	10	<b>TO</b>
				1	10:1
<b>ID LOGO</b>	<b>SL HZ</b>	1	<b>VT</b>	20	<b>TO</b>
				1	20:1
			<b>QR</b>		
<b>YR</b>					



CD0005




LOW VOLTAGE  
(2Y)



LINE

HIGH VOLTAGE  
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS