

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIREL-CAGE INDUCTION

FRAME G405T

ENCLOSURE: X/P, UNDERWRITERS LISTED



INCLUDES 404T FRAME MOUNTING HOLES
STD CAST IRON C/BOX

COOLING: FAN COOLED


MOUNTING: FOOT, F-1

CL1-GROUP C&D - CL2-GROUP E,F & G

ENCLOSURE ENHANCEMENT: SEVERE DUTY




Ø 3/8-16 TAP
Ø 1/2-13 TAP
GROUND HOLES



(1) OBSTRUCTION MUST NOT ENCROACH AIR INLET
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.

MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF
STANDARD SHAFT EXTENSION IS .003 MAX. T.I.R.

WEIGHT: 1400 LBS ± 15% DEPENDING ON RATING.



TACONITE SLINGER
BOTH ENDS

DIMENSIONS ARE IN INCHES.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: NEW			
REV: -	VERSION: 00	REVISED: 02:31:08 02/07/2019	TDR: 000001098248
MODEL NO. 617433-605		REF: -	
BY: RAGJSS1	Material: -		

BALDOR

G405T/404T XP F1 FT- CL1 GRP C&D - CL2 GRP E,F&G