ABB BALDOR RELIANCE

Customer information packet

CPX441546T

150//125HP, 1785//1485RPM, 3PH, 60//50HZ, 44
Class - CLI GP C,D; CLII GP E,F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
9/7/2026 4:28:31 AM

Specifications

Enclosure	TEFC
Frame	445T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D; CLII GP E,F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	150.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
	CSA
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Constant Torque Speed Range	10-60
Current @ Voltage	169.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.8 %
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	169.0 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	IP55

Part Detail

Revision	E
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A44WG3335
Layout	617426-350
Eff. date	01-07-2026
CD Diagram	416820-036
Poles	04
Leads	3#1/0
Proprietary	False
Created date	02-13-2019

KVA Code	F
Max Speed	3600 rpm
Motor Lead Quantity/Wire Size	3 @ 1/0 AWG
Motor Standards	NEMA
Motor Type	A4488M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	44.97 IN
Power Factor	86
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	3.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1785 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat

Nameplate

NP2496L
MOBIL POLYREX EM

000613006PC			
CLASS I GROUP	C D X	**NO.**	
CLASS II GROUP	E F G		
OPERATING TEMP CODE	T3C		

000901002AAA	
SUIT @ 55C AMB AT 1.00 SF AT S	INEWAVE

NP3140L												
SPEC NO.	A44-9214-3335			**CAT.NO.**	CPX441546T					**FRAME**	445T	
HP	150	**VOLTS**	460		**PHASE**	3	**DESIGN**	B	**TYPE**	P		
RPM	1785	**AMPS**	169		**HZ**	60	**AMB**	40	**SF**	1.00		
DRIVE END BEARING	90BC03J30X			**DUTY**	CONT		**INSUL.CLASS**	F				
OPP D.E. BEARING	90BC03J30X			**ENCL**	TEFC	**CODE**	F					
SF	1.15	**WK2**	51.1	**MAG CUR**	48.9		**RPM MAX**	3600				
CT HZ	10-60	**VT HZ**	0-60	**CHP HZ**	60-90		**NEMA-NOM-EFF**	95.8				
	IP66											
SER.NO.				**MOTOR WEIGHT**								

S/O	FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS
	445T	150	P	3/60	1785	460

AMPS	DUTY	AMB °C/ INSUL	S.F.	NEMA DESIGN	CODE LETTER	ENCLOSURE
169	CONT	40/F	1.15	B	F	TEFC

E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES. @25 °C OHMS (BETWEEN LINES)
498808	418143053AE	---	---	.0298

PERFORMANCE

LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY
NO LOAD	0	48.9	1800	4.26	0
1/4	37.6	69.1	1796	54.3	93.6
2/4	75.0	97.1	1792	75.6	95.7
3/4	112	131	1788	83.4	96.0
4/4	150	169	1784	86.5	95.8
5/4	188	210	1779	87.6	95.3

SPEED TORQUE

	RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES
LOCKED ROTOR	0	130	572	1041
PULL UP	270	116	511	1020
BREAKDOWN	1729	280	1237	579
FULL LOAD	1784	100	442	169

AMPERES SHOWN FOR 460 VOLT CONNECTION. IF OTHER CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

TYPICAL DATA
NEMA NOMINAL EFFICIENCY = 95.8 PCT.

ABB	DRAWN BY: C.B.ATANGANE CHECKED BY: C.E.JAMISON APPROVED BY: C.E.JAMISON DATE: 10/16/23	AC MOTOR PERFORMANCE DATA	A44WG3335-R001 DATE ISSUED 02/03/25

FRAME 445T	RPM 1785	S.F. 1.15	ROTOR 418143053AE
HP 150	VOLTS 460	NEMA DESIGN B	TEST S.O. TYPICAL DATA
TYPE P	AMPS 169	CODE LETTER F	TEST DATE ---
PHASE / HERTZ 3/60	DUTY CONT	ENCLOSURE TEFC	STATOR RES. @ 25°C .0298
	AMB °C / INSUL 40/F	E/S 498808	OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

ABB	DRAWN BY: C.B.ATANGANE CHECKED BY: C.E.JAMISON APPROVED BY: C.E.JAMISON DATE: 10/16/23	AC MOTOR PERFORMANCE DATA	A44WG3335-R001 ISSUE DATE 02/03/25

FRAME 445T	RPM 1785	S.F. 1.15	ROTOR 418143053AE
HP 150	VOLTS 460	NEMA DESIGN B	TEST S.O. TYPICAL DATA
TYPE P	AMPS 169	CODE LETTER F	TEST DATE ---
PHASE / HERTZ 3/60	DUTY CONT	ENCLOSURE TEFC	STATOR RES. @ 25°C .0298
	AMB °C / INSUL 40/F	E/S 498808	OHMS (BETWEEN LINES)



THERMAL LIMIT CURVE
NEMA NOMINAL EFFICIENCY = 95.8 PCT.

AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

ABB	DRAWN BY: C.B.ATANGANE CHECKED BY: C.E.JAMISON APPROVED BY: C.E.JAMISON DATE: 10/16/23	AC MOTOR PERFORMANCE DATA	A44WG3335-R001 ISSUE DATE 02/03/25

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION

617426-350

ENCLOSURE: UL LISTED MOTOR

MOUNTING: F-1 FOOT

G444T/G445T FRAME MOUNTING HOLES

CLASS 1: GR. C&D, CLASS 2: GR. E,F,&G

ENCLOSURE ENHANCEMENT: SEVERE DUTY

COOLING: FAN COOLED









DIMENSIONS ARE IN INCHES.
WEIGHT (LBS): 2150. WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

1 OBSTRUCTION MUST NO ENCROACH ON AIR INLETMOTOR.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

SHEET NUMBER 1 OF 1

617426-350

REV. DESC: NEW			
REV: -	VERSION: 00	REVISED: 02:20:28 02/12/2019	TDR: 000001098250
MODEL NO. 617426-350			REF:
BY: RAGJSS1	Material:		C

BALDOR

G445/444T TEFC XP F1 FT-CI-CB - CL.1 GR.C&D CL.2 GR.E,F&G

617426-350


CONNECTION DIAGRAM
ACCESSORIES
MOTOR WINDING THERMOSTATS
CONTACTS ____ @ ____ °C
FIGURE NUMBER ____
CONTACT RATING
VOLTS
110-120
220-240
440-480
550-600
CONTINUOUS AMPERES
3.0
1.5
0.75
0.60
INRUSH AMPERES
30
15
7.5
6.0
418174-006
THERMOSTATS
NORMALLY CLOSED
NORMALLY OPEN
FIGURE 1
FIGURE 2
FIGURE 3
FIGURE 4
FIGURE 5
FIGURE 6
FIGURE 7
FIGURE 8
P1
P2
418174-006
CUSTOMER ____
CUSTOMER ORDER NO. ____
S.O. NO. ____
REV. DESC: LOADED TO BUS
REV. LTR: A
VERSION: 01
TDR: 000000570390
FILE: \RAG\00013\849
REVISED: 10:16:21 12/07/2010
BY: RAGDRF
MTL: -
BALDOR
A-C MOTOR CONNECTION ACCESSORIES
SH 1 of 1

416820–036

A–C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575–BA)

416820–036

REV. DESC: LOADED TO BUS, C/R 335225			BALDOR
REV. LTR: –	VERSION: 00	TDR: 000000538207	
FILE: \MGA\00000\682		REVISED: 11:54:06 04/30/2010	CONN DIAG – STANDARD 3 LEAD
MTL: –		BY: RAGRA	SH 1 of 1