



- NOTES:
- SHAFT STANDARDS PER 3425
 - ▽ X/P SURFACE PER DWG. 402111-A

TOLERANCE UNLESS OTHERWISE SHOWN:	
ONE PLACE DECIMAL	±0.1
TWO PLACE DECIMAL	±0.02
THREE PLACE DECIMAL	±0.003
ANGLE	±0°-30'
SURFACE FINISH	250



1	CORE KEY	34180-160	GA		
1	FINISHED SHAFT	4.25 X 50.99		FSCLI	158.7
RA	NAME	SIZE OR CASTING	SYM	46024-	WT. (LB.)

BALDOR-DODGE-RELIANCE PROPRIETARY & CONFIDENTIAL: THIS DRAWING IS THE PROPERTY OF BALDOR-DODGE-RELIANCE AND/OR ITS SUBSIDIARIES AND IS NOT TO BE USED, DUPLICATED OR DISCLOSED WITHOUT THE EXPRESS WRITTEN PERMISSION OF THE COMPANY.		REV. DESC: UPDATING THE ODE BEARING LENGTH			
		REV: A	VERSION: 01	REVISED: 02:32:00 08/24/2015	TDR: 000000940797
		MODEL NO. 611767-460			REF:
		BY: RAGRA	Material: FSCLI		

BALDOR

G449T SHAFT 6318-6318 XP - CL 1 GR. C

611767-460

611767-460