

DUTY MASTER ALTERNATING CURRENT MOTORS





SQUIRREL-CAGE INDUCTION

ENCLOSURE: EXPLOSION PROOF

MOUNTING: FOOT, F-1 SIDE

G449T/G447T FRAME MOUNTING HOLES

COOLING: FAN COOLED



⊙ CENTER OF GRAVITY MAY VARY ± 1.00.

DIMENSIONS ARE IN INCHES.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: NEW DRAWING			
REV: -	VERSION: 00	REVISED: 09:19:46 09/10/2018	TDR: 000001083107
MODEL NO. 617426-329			
BY: USJEDIL			

BALDOR

G449/447T FCXP F1 FOOT CI CONDUIT BOX W/ 4 NPT/TACONITE SLGR

(1) OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.

MOTOR WEIGHT (LBS) = 3180 ± 15% DEPENDING ON RATING.

MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R