

**BALDOR • RELIANCE**

---

# Customer information packet

## CSPM3158T-G

3HP, 3465RPM, 3PH, 60HZ, 145TC, 3540M, OPSB, F1

Class - None

Division - Not Applicable

## Specifications

Enclosure	OPSB
Frame	145TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.450 A @ 460.0 V 6.900 A @ 230.0 V 7.900 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	88.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	3.5 a

## Part detail

Revision	B
Type	AC
Mech. spec.	35E6893
Base	
Status	PRD/A
Elec. spec.	35WGZ969
Layout	35LYE6893
Eff. date	12-01-2025
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	04-03-2025

Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3540M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	14.38 IN
Power Factor	92
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3465 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None



**AC Induction Motor Performance Data**

Record # 112316

Preliminary Data Sheet

<b>Winding:</b> 35WGZ969-R004		<b>Type:</b> 3540M		<b>Enclosure:</b> OPSB	
<b>Nameplate Data</b>			<b>460 V, 60 Hz: High Voltage Connection</b>		
<b>Rated Output (HP)</b>		3	<b>Full Load Torque</b>		4.53 LB-FT
<b>Volts</b>		230/460	<b>Start Configuration</b>		direct on line
<b>Full Load Amps</b>		6.9/3.45	<b>Breakdown Torque</b>		21.4 LB-FT
<b>R.P.M.</b>		3465	<b>Pull-up Torque</b>		12.2 LB-FT
<b>Hz</b>	60	<b>Phase</b>	3	<b>Locked-rotor Torque</b>	19.3 LB-FT
<b>NEMA Design Code</b>	B	<b>KVA Code</b>	K	<b>Starting Current</b>	34.6 A
<b>Service Factor (S.F.)</b>		1.25	<b>No-load Current</b>		1.29 A
<b>NEMA Nom. Eff.</b>	88.5	<b>Power Factor</b>	92	<b>Line-line Res. @ 25°C</b>	3.62 Ω
<b>Rating - Duty</b>		40C	AMB-CONT	<b>Temp. Rise @ Rated Load</b>	32°C
<b>S.F. Amps</b>		9/4.5		<b>Temp. Rise @ S.F. Load</b>	42°C
				<b>Locked-rotor Power Factor</b>	42.1
				<b>Rotor inertia</b>	0.111 lb-ft <sup>2</sup>

**Load Characteristics 460 V, 60 Hz, 3 HP**

<b>% of Rated Load</b>	<b>25</b>	<b>50</b>	<b>75</b>	<b>100</b>	<b>125</b>	<b>150</b>	<b>S.F.</b>
<b>Power Factor</b>	59	79	86	90	92	92	92
<b>Efficiency</b>	74.3	82.9	85.4	86	85.6	84.8	85.6
<b>Speed</b>	3568	3541	3513	3483	3450	3414	3450
<b>Line amperes</b>	1.6	2.16	2.86	3.63	4.48	5.39	4.48


ABB Motors and Mechanical Inc.

WINDING # 35WGZ969


3 HP 3 PH 60 HZ 3465 RPM 460 V 3540M

Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=21.4 PU=12.2 LR=19.3 LRA=34.6




6/17/2026 ACPERF, record # 112316



CD0005



LOW VOLTAGE  
(2Y)



LINE

HIGH VOLTAGE  
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

**BALDOR ELECTRIC Co.**

3PH, DV, 9 LEADS