ABB BALDOR RELIANCE

Customer information packet

CSPM3212T

5HP, 3490RPM, 3PH, 60HZ, 182TC, 3634M, OPSB, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/18/2026 5:16:31 PM

Specifications

Enclosure	OPSB
Frame	182TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM 4
	WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	11.200 A @ 230.0 V
	12.200 A @ 208.0 V
	5.600 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	5.6 a

Part Detail

Revision	C
Type	AC
Mech. spec.	36P419
Base	
Status	PRD/A
Elec. spec.	36WGT826
Layout	36LYP419
Eff. date	03-19-2026
CD Diagram	CD0005
Poles	02
Leads	9#16
Proprietary	False
Created date	01-02-2024

Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	L
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3634M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	14.99 IN
Power Factor	93
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3490 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4423A01A01L												
CAT #	CSPM3212T			**WGT**	81	**LBS**						
SPEC	36P419T826			**ENCL**	OPSB							
SER #				**CC**	010A	**IP**	23					
HP	5		**MAG CUR**	11.2/5.6								
VOLTS	230/460				**NEMA NOM. EFF**	91						
AMPS	11.2/5.6			**PF**	93							
RATING	40C AMB-CONT											
RPM	3490			**MAX RPM**	5400							
FRAME	182TC	**HZ**	60	**CODE**	L	**CLASS**	F					
SER.F.	1.15	**SF AMP**		**PH**	3	**DES**	A					
DE	6206	**ODE**	6205									
LUBRICATION	POLYREX EM											
ID LOGO	**INVERTER TYPE**		**VPWM**	**CHP**	60	**TO**	90	1.5:1				
ID LOGO	**WK2**	0.15	**CT**	6	**TO**	60	10:1					
ID LOGO	**SL HZ**	1.8	**VT**	3	**TO**	60	20:1					
					QR							
YR												

AC Induction Motor Performance Data
Record # 100980
Typical performance - not guaranteed values

Winding: 36WGT826-R009	**Type:** 3634M	**Enclosure:** OPSB

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			5	**Full Load Torque**	7.6 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			11.2/5.6	**Breakdown Torque**	41.6 LB-FT
R.P.M.			3490	**Pull-up Torque**	26 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	30.5 LB-FT
NEMA Design Code	A	**KVA Code**	L	**Starting Current**	59.9 A
Service Factor (S.F.)			1.15	**No-load Current**	1.61 A
NEMA Nom. Eff.	91	**Power Factor**	93	**Line-line Res. @ 25ºC**	2.17 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	24°C
S.F. Amps				**Temp. Rise @ S.F. Load**	31°C
				Locked-rotor Power Factor	43.2
				Rotor inertia	0.152 lb-ft²

Load Characteristics 460 V, 60 Hz, 5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	63	83	90	93	94	95	94
Efficiency	89.2	92	91.9	91.1	89.8	88.3	90.3
Speed	3572	3546	3518	3490	3458	3423	3471
Line amperes	2.16	3.15	4.32	5.58	6.96	8.51	6.41


ABB Motors and Mechanical Inc.

WINDING # 36WGT826


Typical performance - not guaranteed values.

5 HP 3 PH 60 HZ 3490 RPM 460 V 3634M


TORQUES(LB-FT): PO=41.6 PU=26 LR=30.5 LRA=59.9




11/18/2026 ACPERF, record # 100980


36LYP419
614-634 = 14.99
635-648 = 16.50
647-648 = 16.93
2.75
.25
2.62
2.72
.25 KEY
2.12 LONG
Ø 8.500
Ø 8.497
Ø 1.1250
1.1245
8.82
6 HOLES
.44 DIA.
4.50
3.50
5.50
.50
6.50
Ø7.86
6.82
2.30
45°
45°
8.43
4.50 +.00 -.06
4 HOLES
.50-13 TAP
Ø7.25 B.C.
LEAD HOLE
1.09 DIA.
3.75
3.75
5.76
4.31
8.63
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: NEW
REV: - VERSION: 00 REVISED: 09:32:50 01/03/2024 TDR: 000001223000
MODEL NO. 36LYP419 REF: -
BY: USALMAZ B
BALDOR - RELIANCE®
HORZ 182-4TC OPSB 36M GFL BRGS, 'A64 NP, IBLT
36LYP419

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS