

ABB BALDOR RELIANCE III

Customer information packet

CSPM3546

1HP, 1770RPM, 3PH, 60HZ, 56HC, 3520M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56HC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM 4 WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.600 A @ 460.0 V 3.200 A @ 208.0 V 3.200 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	85.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.6 a

Part Detail

Revision	B
Type	AC
Mech. spec.	35E6402
Base	
Status	PRD/A
Elec. spec.	35WGG004
Layout	35LYE6402
Eff. date	11-19-2025
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	01-10-2024

Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3520M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.22 IN
Power Factor	69
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4423A01A01L														
CAT #	CSPM3546					WGT	37	LBS						
SPEC	35E6402G004					ENCL	TEFC							
SER #						CC	010A	IP	54					
HP	1	MAG CUR				2.2/1.1								
VOLTS	230/460					NEMA NOM. EFF				85.5				
AMPS	3.2/1.6					PF	69							
RATING	40C AMB-CONT													
RPM	1770					MAX RPM		2700						
FRAME	56HC	HZ	60	CODE		N	CLASS		F					
SER.F.	1.15	SF AMP	3.4/1.7			PH	3	DES	B					
DE	6205		ODE		6203									
LUBRICATION	POLYREX EM													
ID LOGO	INVERTER TYPE				VPWM		CHP	60	TO	90	1.5:1			
ID LOGO	WK2	0.144	CT	6	TO	60	10:1							
ID LOGO	SL HZ	1.07	VT	3	TO	60	20:1							
						QR								
YR														

AC Induction Motor Performance Data

Record # 91625

Typical performance - not guaranteed values

Winding: 35WGG004-R001			Type: 3520M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		1	Full Load Torque		2.982 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		3.2/1.6	Breakdown Torque		14.6 LB-FT		
R.P.M.		1770	Pull-up Torque		7.57 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		9.17 LB-FT	
NEMA Design Code		B	KVA Code		N		
Service Factor (S.F.)		1.15	Starting Current		14.6 A		
NEMA Nom. Eff.		85.5	Power Factor		69		
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		36°C
S.F. Amps		3.4/1.7			Temp. Rise @ S.F. Load		41°C
					Locked-rotor Power Factor		61.549
					Rotor inertia		0.144 lb-ft²

Load Characteristics 460 V, 60 Hz, 1 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	29	45	58	67	73	78	71
Efficiency	71.1	81.2	84.7	85.8	86	85.6	85.9
Speed	1794	1787.3	1781.1	1774.3	1767.4	1759.4	1770
Line amperes	1.22	1.31	1.46	1.64	1.86	2.11	1.77

ABB Motors and Mechanical Inc.

WINDING # 35WGG004

Typical performance - not guaranteed values.

1 HP 3 PH 60 HZ 1770 RPM 460 V 3520M

TORQUES (LB-FT): PO=14.6 PU=7.57 LR=9.17 LRA=14.6





