ABB BALDOR RELIANCE

Customer information packet

CSPM3610T

3HP, 3500RPM, 3PH, 60HZ, 182TC, 3634M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
9/7/2026 4:34:41 AM

Specifications

Enclosure	TEFC
Frame	182TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	WEEE
	NEMA PREMIUM 4
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.400 A @ 460.0 V
	6.800 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	88.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	3.4 a
Insulation Class	F

Part Detail

Revision	B
Type	AC
Mech. spec.	36P427
Base	
Status	PRD/A
Elec. spec.	36WGT562
Layout	36LYP427
Eff. date	11-19-2025
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	01-02-2024

Inverter Code	Inverter Duty
KVA Code	M
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3634M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	16.55 IN
Power Factor	95
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4423A01A01L												
CAT #	CSPM3610T			**WGT**	81	**LBS**						
SPEC	36P427T562			**ENCL**	TEFC							
SER #				**CC**	010A	**IP**	54					
HP	3		**MAG CUR**	1.8/.9								
VOLTS	230/460					**NEMA NOM. EFF**	88.5					
AMPS	6.8/3.4				**PF**	95						
RATING	40C AMB-CONT											
RPM	3500			**MAX RPM**	5400							
FRAME	182TC	**HZ**	60	**CODE**	M	**CLASS**	F					
SER.F.	1.15	**SF AMP**	7.6/3.8		**PH**	3	**DES**	A				
DE	6206		**ODE**	6205								
LUBRICATION	POLYREX EM											
ID LOGO	**INVERTER TYPE**		**VPWM**		**CHP**	60	**TO**	90	1.5:1			
ID LOGO	**WK2**	0.15	**CT**	6	**TO**	60	10:1					
ID LOGO	**SL HZ**	1.7	**VT**	3	**TO**	60	20:1					
						QR						
YR												

AC Induction Motor Performance Data
Record # 100910
Typical performance - not guaranteed values

Winding: 36WGT562-R002	**Type:** 3634M	**Enclosure:** TEFC

Nameplate Data			
Rated Output (HP)			3
Volts			230/460
Full Load Amps			6.8/3.4
R.P.M.			3500
Hz	60	**Phase**	3
NEMA Design Code	A	**KVA Code**	M
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	88.5	**Power Factor**	95
Rating - Duty			40C AMB-CONT
S.F. Amps			7.6/3.8

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	4.55 LB-FT
Start Configuration	direct on line
Breakdown Torque	23.5 LB-FT
Pull-up Torque	15.1 LB-FT
Locked-rotor Torque	16.9 LB-FT
Starting Current	38.2 A
No-load Current	0.87 A
Line-line Res. @ 25ºC	3.58 Ω
Temp. Rise @ Rated Load	35°C
Temp. Rise @ S.F. Load	42°C
Locked-rotor Power Factor	42
Rotor inertia	0.153 lb-ft²

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	72	87	93	95	96	97	96
Efficiency	82.5	87.9	89.1	88.7	88.4	87.3	88.5
Speed	3574	3551	3526	3500	3473	3442	3484
Line amperes	1.26	1.88	2.58	3.38	4.15	5.02	3.84

ABB Motors and Mechanical Inc.

WINDING # 36WGT562

3 HP 3 PH 60 HZ 3500 RPM 460 V 3634M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=23.5 PU=15.1 LR=16.9 LRA=38.2



9/7/2026 ACPERF, record # 100910


36LYP427
614-623 = 15.18
624-634 = 16.55
635-646= 18.04
647-648 = 18.48
4.27
2.75
.25
2.62
.25 KEY
1.75 LONG
Ø8.60
Ø8.500
8.497
8.85
Ø1.1250
1.1245
6 HOLES
.41 DIA.
4.50
.50
5.50
3.50
6.50
DRAIN FITTINGS
(EA. END)
Ø7.86
6.86
2.43
45°
45°
8.43
4.50+.00
-.06
4 HOLES
.50-13 TAP
Ø7.25 B.C.
LEAD HOLE
1.09 DIA.
3.75
3.75
5.76
4.31
8.63
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: NEW
REV: - VERSION: 00 REVISED: 11:49:26 01/03/2024 TDR: 000001223000
MODEL NO. 36LYP427 REF: -
BY: USALMAZ B
BALDOR - RELIANCE®
HORZ 182-4TC TEFC 36M IP54, GFL BRGS, 'A64 NP, IBOLT
36LYP427

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS