

ABB BALDOR RELIANCE III

Customer information packet

CSPM3314T

15HP, 3515RPM, 3PH, 60HZ, 215TC, 3756M, OPSB, F

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	215TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	WEEE NEMA PREMIUM 4
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	17.000 A @ 460.0 V 34.000 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	17.0 a
Insulation Class	F

Part Detail

Revision	B
Type	AC
Mech. spec.	37T653
Base	
Status	PRD/A
Elec. spec.	37WGR601
Layout	37LYT653
Eff. date	11-19-2025
CD Diagram	CD0180
Poles	02
Leads	9#14
Proprietary	False
Created date	11-29-2023

Inverter Code	Inverter Duty
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3756M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	19.69 IN
Power Factor	88
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3515 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4423A01A01L														
CAT #	CSPM3314T					WGT	187	LBS						
SPEC	37T653R601					ENCL	OPSB							
SER #						CC	010A	IP	23					
HP	15					MAG CUR	11.6/5.8							
VOLTS	230/460									NEMA NOM. EFF	92.4			
AMPS	34/17						PF	88						
RATING	40C AMB-CONT													
RPM	3515					MAX RPM			5400					
FRAME	215TC	HZ	60			CODE	K	CLASS	F					
SER.F.	1.15	SF AMP	39/19.5				PH	3	DES	A				
DE	6307		ODE	6206										
LUBRICATION	POLYREX EM													
ID LOGO	INVERTER TYPE				VPWM		CHP	60	TO	90	1.5:1			
ID LOGO	WK2	0.51	CT	6	TO	60	10:1							
ID LOGO	SL HZ	1.4	VT	3	TO	60	20:1							
							QR							
YR														

AC Induction Motor Performance Data

Record # 100931

Typical performance - not guaranteed values

Winding: 37WGR601-R005				Type: 3756M		Enclosure: ODP		
Nameplate Data				460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		15		Full Load Torque		22.09 LB-FT		
Volts		230/460		Start Configuration		direct on line		
Full Load Amps		34/17		Breakdown Torque		112 LB-FT		
R.P.M.		3515		Pull-up Torque		43.2 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		62 LB-FT		
NEMA Design Code		A	KVA Code	K		Starting Current		161 A
Service Factor (S.F.)		1.15		No-load Current		5.75 A		
NEMA Nom. Eff.		92.4	Power Factor	88		Line-line Res. @ 25°C		0.406 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		40°C		
S.F. Amps		39/19.5		Temp. Rise @ S.F. Load		49°C		
				Locked-rotor Power Factor		29.9		
				Rotor inertia		0.51 lb-ft²		

Load Characteristics 460 V, 60 Hz, 15 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	53	76	85	88	90	90	89
Efficiency	89.4	92.8	93.2	92.7	91.9	90.8	92.2
Speed	3580	3561	3539	3516	3491	3465	3501
Line amperes	6.81	9.54	13.1	16.95	20.9	25.31	19.3


ABB Motors and Mechanical Inc.

WINDING # 37WGR601



Typical performance - not guaranteed values.

15 HP 3 PH 60 HZ 3515 RPM 460 V 3756M

TORQUES (LB-FT): PO=112 PU=43.2 LR=62 LRA=161



CD0180


 LOW VOLTAGE
(2D)

 HIGH VOLTAGE
(1D)

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007

REV. LTR: D

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\148

REVISED: 10: 25: 29 02/19/2019

BY: ENBRIRO

MTL: —


BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1