

# ABB BALDOR RELIANCE III

---

## Customer information packet

### CSPM3556T

1HP, 1170RPM, 3PH, 60HZ, 145TC, 3532M, TEFC, F1

Class - None

Division - Not Applicable

**Specifications**

|                                       |                                                             |
|---------------------------------------|-------------------------------------------------------------|
| <b>Enclosure</b>                      | TEFC                                                        |
| <b>Frame</b>                          | 145TC                                                       |
| <b>Frame Material</b>                 | Steel                                                       |
| <b>Frequency</b>                      | 60.00 Hz                                                    |
| <b>Haz Area Class and Group</b>       | None                                                        |
| <b>Haz Area Division</b>              | Not Applicable                                              |
| <b>Motor Letter Type</b>              | Three Phase                                                 |
| <b>Output @ Frequency</b>             | 1.000 HP @ 60 HZ                                            |
| <b>Phase</b>                          | 3                                                           |
| <b>Synchronous Speed @ Frequency</b>  | 1200 RPM @ 60 HZ                                            |
| <b>Voltage @ Frequency</b>            | 230.0 V @ 60 HZ<br>460.0 V @ 60 HZ                          |
| <b>Agency Approvals</b>               | NEMA PREMIUM 4<br>WEEE                                      |
| <b>Ambient Temperature</b>            | 40 °C                                                       |
| <b>Auxiliary Box</b>                  | NO AUXILLARY BOX                                            |
| <b>Auxiliary Box Lead Termination</b> | None                                                        |
| <b>Base Indicator</b>                 | Rigid                                                       |
| <b>Bearing Grease Type</b>            | Polyrex EM (-20F +300F)                                     |
| <b>Blower</b>                         | None                                                        |
| <b>Current @ Voltage</b>              | 1.660 A @ 460.0 V<br>3.320 A @ 230.0 V<br>3.500 A @ 208.0 V |
| <b>Design Code</b>                    | B                                                           |
| <b>Drip Cover</b>                     | No Drip Cover                                               |
| <b>Duty Rating</b>                    | CONT                                                        |
| <b>Efficiency @ 100% Load</b>         | 84.0 %                                                      |
| <b>Electrically Isolated Bearing</b>  | Not Electrically Isolated                                   |
| <b>Feedback Device</b>                | NO FEEDBACK                                                 |
| <b>Front Shaft Indicator</b>          | None                                                        |
| <b>Heater Indicator</b>               | No Heater                                                   |
| <b>High Voltage Full Load Amps</b>    | 1.7 a                                                       |

**Part Detail**

|                     |            |
|---------------------|------------|
| <b>Revision</b>     | D          |
| <b>Type</b>         | AC         |
| <b>Mech. spec.</b>  | 35E6390    |
| <b>Base</b>         |            |
| <b>Status</b>       | PRD/A      |
| <b>Elec. spec.</b>  | 35WGG824   |
| <b>Layout</b>       | 35LYE6390  |
| <b>Eff. date</b>    | 11-19-2025 |
| <b>CD Diagram</b>   | CD0005     |
| <b>Poles</b>        | 06         |
| <b>Leads</b>        | 9#18       |
| <b>Proprietary</b>  | False      |
| <b>Created date</b> | 01-08-2024 |

|                                      |                            |
|--------------------------------------|----------------------------|
| <b>Insulation Class</b>              | <b>F</b>                   |
| <b>Inverter Code</b>                 | <b>Inverter Duty</b>       |
| <b>KVA Code</b>                      | <b>J</b>                   |
| <b>Lifting Lugs</b>                  | <b>No Lifting Lugs</b>     |
| <b>Locked Bearing Indicator</b>      | <b>Locked Bearing</b>      |
| <b>Max Speed</b>                     | <b>1800 rpm</b>            |
| <b>Motor Lead Quantity/Wire Size</b> | <b>9 @ 18 AWG</b>          |
| <b>Motor Lead Termination</b>        | <b>Flying Leads</b>        |
| <b>Motor Standards</b>               | <b>NEMA</b>                |
| <b>Motor Type</b>                    | <b>3532M</b>               |
| <b>Mounting Arrangement</b>          | <b>F1</b>                  |
| <b>Number of Poles</b>               | <b>6</b>                   |
| <b>Overall Length</b>                | <b>14.19 IN</b>            |
| <b>Power Factor</b>                  | <b>67</b>                  |
| <b>Product Family</b>                | <b>General Purpose</b>     |
| <b>Pulley End Bearing Type</b>       | <b>Ball</b>                |
| <b>Pulley Face Code</b>              | <b>C-Face</b>              |
| <b>Pulley Shaft Indicator</b>        | <b>Standard</b>            |
| <b>Rodent Screen</b>                 | <b>None</b>                |
| <b>RoHS Status</b>                   | <b>ROHS COMPLIANT</b>      |
| <b>Service Factor</b>                | <b>1.15</b>                |
| <b>Shaft Diameter</b>                | <b>0.875 IN</b>            |
| <b>Shaft Ground Indicator</b>        | <b>No Shaft Grounding</b>  |
| <b>Shaft Rotation</b>                | <b>Reversible</b>          |
| <b>Shaft Slinger Indicator</b>       | <b>No Slinger</b>          |
| <b>Speed</b>                         | <b>1170 rpm</b>            |
| <b>Speed Code</b>                    | <b>Single Speed</b>        |
| <b>Starting Method</b>               | <b>Direct on line</b>      |
| <b>Thermal Device - Bearing</b>      | <b>None</b>                |
| <b>Thermal Device - Winding</b>      | <b>None</b>                |
| <b>Vibration Sensor Indicator</b>    | <b>No Vibration Sensor</b> |
| <b>Winding Thermal 1</b>             | <b>None</b>                |
| <b>Winding Thermal 2</b>             | <b>None</b>                |

**Nameplate**

| NP4423A01A01L |               |         |           |      |      |               |       |      |     |       |    |  |  |
|---------------|---------------|---------|-----------|------|------|---------------|-------|------|-----|-------|----|--|--|
| CAT #         | CSPM3556T     |         |           |      |      | WGT           | 47    | LBS  |     |       |    |  |  |
| SPEC          | 35E6390G824   |         |           |      |      | ENCL          | TEFC  |      |     |       |    |  |  |
| SER #         |               |         |           |      |      | CC            | 010A  | IP   | 54  |       |    |  |  |
| HP            | 1             | MAG CUR |           |      |      | 2.06/1.03     |       |      |     |       |    |  |  |
| VOLTS         | 230/460       |         |           |      |      | NEMA NOM. EFF |       |      |     |       | 84 |  |  |
| AMPS          | 3.32/1.66     |         |           |      |      | PF            | 67    |      |     |       |    |  |  |
| RATING        | 40C AMB-CONT  |         |           |      |      |               |       |      |     |       |    |  |  |
| RPM           | 1170          |         |           |      |      | MAX RPM       |       | 1800 |     |       |    |  |  |
| FRAME         | 145TC         | HZ      | 60        | CODE |      | J             | CLASS |      | F   |       |    |  |  |
| SER.F.        | 1.15          | SF AMP  | 3.68/1.84 |      |      |               | PH    | 3    | DES | B     |    |  |  |
| DE            | 6205          |         | ODE       |      | 6203 |               |       |      |     |       |    |  |  |
| LUBRICATION   | POLYREX EM    |         |           |      |      |               |       |      |     |       |    |  |  |
| ID LOGO       | INVERTER TYPE |         |           | VPWM |      | CHP           | 60    | TO   | 90  | 1.5:1 |    |  |  |
| ID LOGO       | WK2           | 0.232   | CT        | 6    | TO   | 60            | 10:1  |      |     |       |    |  |  |
| ID LOGO       | SL HZ         | 1.57    | VT        | 3    | TO   | 60            | 20:1  |      |     |       |    |  |  |
|               |               |         |           |      |      |               |       |      |     |       |    |  |  |
|               |               |         |           |      |      |               |       |      |     |       |    |  |  |
|               |               |         |           |      |      |               |       |      |     |       |    |  |  |
|               |               |         |           |      |      |               |       |      |     |       |    |  |  |
|               |               |         |           |      |      |               | QR    |      |     |       |    |  |  |
| YR            |               |         |           |      |      |               |       |      |     |       |    |  |  |

**AC Induction Motor Performance Data**

Record # 100796

Typical performance - not guaranteed values

| Winding: 35WGG824-R001 |    |              | Type: 3532M                              |                           | Enclosure: TEFC       |              |        |
|------------------------|----|--------------|------------------------------------------|---------------------------|-----------------------|--------------|--------|
| Nameplate Data         |    |              | 460 V, 60 Hz:<br>High Voltage Connection |                           |                       |              |        |
| Rated Output (HP)      |    | 1            | Full Load Torque                         |                           | 4.47 LB-FT            |              |        |
| Volts                  |    | 230/460      | Start Configuration                      |                           | direct on line        |              |        |
| Full Load Amps         |    | 2.06/1.03    | Breakdown Torque                         |                           | 12.7 LB-FT            |              |        |
| R.P.M.                 |    | 1170         | Pull-up Torque                           |                           | 7.4 LB-FT             |              |        |
| Hz                     | 60 | Phase        | 3                                        | Locked-rotor Torque       |                       | 9 LB-FT      |        |
| NEMA Design Code       |    | B            | KVA Code                                 | J                         | Starting Current      |              | 9.5 A  |
| Service Factor (S.F.)  |    | 1.15         |                                          | No-load Current           |                       | 1.03 A       |        |
| NEMA Nom. Eff.         |    | 84           | Power Factor                             | 67                        | Line-line Res. @ 25°C |              | 18.3 Ω |
| Rating - Duty          |    | 40C AMB-CONT |                                          | Temp. Rise @ Rated Load   |                       | 42°C         |        |
| S.F. Amps              |    | 3.68/1.84    |                                          | Temp. Rise @ S.F. Load    |                       | 50°C         |        |
|                        |    |              |                                          | Locked-rotor Power Factor |                       | 45.8         |        |
|                        |    |              |                                          | Rotor inertia             |                       | 0.232 lb-ft² |        |

**Load Characteristics 460 V, 60 Hz, 1 HP**

| % of Rated Load | 25   | 50   | 75   | 100  | 125  | 150  | S.F. |
|-----------------|------|------|------|------|------|------|------|
| Power Factor    | 29   | 46   | 59   | 67   | 72   | 75   | 70   |
| Efficiency      | 74.5 | 82.7 | 84.4 | 84.2 | 82.9 | 80.7 | 83.4 |
| Speed           | 1193 | 1186 | 1179 | 1171 | 1162 | 1151 | 1166 |
| Line amperes    | 1.08 | 1.21 | 1.41 | 1.66 | 1.96 | 2.32 | 1.84 |

ABB Motors and Mechanical Inc.

WINDING # 35WGG824

Typical performance - not guaranteed values.

1 HP 3 PH 60 HZ 1170 RPM 460 V 3532M

TORQUES (LB-FT): PO=12.7 PU=7.4 LR=9 LRA=9.5





