ABB BALDOR RELIANCE

Customer information packet

CSPM4115T

50HP, 1775RPM, 3PH, 60HZ, 326TC, 1288M, TEFC, F
Class - CLI GP A,B,C,D CLII GP F,G
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/12/2026 10:07:51 PM

Specifications

Enclosure	TEFC
Frame	326TC
Frame Material	Cast Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D CLII GP F,G
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CSA
	CURUSEEV
	NEMA_PREMIUM
	WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	120.000 A @ 230.0 V
	60.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Haz Area Temp Code	T3C

Part Detail

Revision	C
Type	AC
Mech. spec.	12T118
Base	
Status	PRD/A
Elec. spec.	12WGZ340
Layout	12LYT118
Eff. date	04-17-2026
CD Diagram	CD0180
Poles	04
Leads	9#6
Proprietary	False
Created date	09-20-2024

Heater Indicator	No Heater
High Voltage Full Load Amps	60.0 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	9 @ 6 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1288M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	30.71 IN
Power Factor	84
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	2.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP4439B05C23L

CAT # CSPM4115T **SER #** **CC** 010A **WGT** 720 **LBS**

SPEC 12T118Z340 **FRAME** 326TC **ENCL** TEFC **IP** 55

RATING 40C AMB-CONT **NEMA NOM. EFF** 95.4

HP 50 **VOLTS** 230/460

AMPS 116/58 **RPM** 1775 **HZ** 60

PH 3 **CL** F **CODE** J **DES** A **PF** 84 **%** **SER.F.** 1.15 **SF AMP**

DE BRG 6312 **ODE BRG** 6312 **LUBE** POLYREX EM

INV TYPE: **VPWM** **SL HZ** 0.8 **CHP** 60 **TO** 90 1.5:1

WK2 11.7 **LBFT2** **MAX RPM** 2700 **CT** 6 **TO** 60 10:1

MAG CUR 42/21 **VT** 3 **TO** 60 20:1

MEETS INTENT OF IEEE-45 **FOR WEATHER PROTECTION**

CL I DIV 2 GRPS A,B,C,D **TEMP CODE** T3C **CL I INV TEMP CODE** T3 **TEMP=** 200 **C**

CL I ZONE 2 GRPS **IIA,IIB,IIC** **TEMP =** 160 **C** **CL II INV TEMP CODE** T3 **TEMP =** 200 **C**

CL II DIV 2 GRPS F&G **TEMP CODE** T3C **1.0 SF ON PWM INVERTER** **POWER**

CL II ZONE 22 GRPS IIIB **TEMP=** 160 **C**

YR


AC Induction Motor Performance Data
Record # 107565
Typical performance - not guaranteed values


Winding: 12WGZ340-R001	**Type:** 1288M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			50	**Full Load Torque**	147.7 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			120/60	**Breakdown Torque**	506 LB-FT
R.P.M.			1775	**Pull-up Torque**	272 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	269 LB-FT
NEMA Design Code	A	**KVA Code**	J	**Starting Current**	436 A
Service Factor (S.F.)			1.15	**No-load Current**	21.8 A
NEMA Nom. Eff.	95.4	**Power Factor**	84	**Line-line Res. @ 25ºC**	0.094907 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	57°C
S.F. Amps				**Temp. Rise @ S.F. Load**	70°C
				Locked-rotor Power Factor	25.3


Load Characteristics 460 V, 60 Hz, 50 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	49	71	81	85	86	87	86
Efficiency	93.3	95.5	95.9	95.7	95.2	94.6	95.4
Speed	1794.8	1790	1784.7	1779.7	1772.9	1766.3	1776
Line amperes	25.7	34.4	45.4	57.7	71.2	85.5	65.8



ABB Motors and Mechanical Inc.
WINDING # 12WGZ340
50 HP 3 PH 60 HZ 1775 RPM 460 V 1288M
Typical performance - not guaranteed values.
TORQUES(LB-FT): PO=506 PU=272 LR=269 LRA=436
TORQUE
RPM
KW
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
KW
AMPS
PERCENT OF RATED OUTPUT (50 HP)
11/12/2026 ACPERF, record # 107565


12LYT118
(1232-1280) = 30.71
(1282-1288 4 POLE ONLY)
14.21
.25
5.00
.50 KEY
3.88 LONG
Ø13.40
Ø12.500
12.497
2.125
2.124
GND
LOC.
10.50
10.50
1.00
12.00
5.25
14.00
DRAIN FITTING
HW4505A02
(EA. END)
17.81
14.26
8.46
PLUG
(EA. END)
3.22
45°
45°
16.23
8.00 +.00 -.06
LEAD HOLE
2.00 N.P.T.
8 HOLES
Ø.66
6.25
6.25
11.75
7.25
14.50
4 HOLES
.62-11 TAP
1.00 DEEP
ON Ø11.00 B.C.
1 PIN
HW3023E06
(EA. END)
6312
ODE SEAL DETAIL
6312
DE SEAL DETAIL
TACONITE
SEAL
(EA. END)
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: NEW
REV: - VERSION: 00 REVISED: 10:34:15 10/17/2024 TDR: 000001239216
MODEL NO. 12LYT118 REF: -
BY: USALLIN3 B
BALDOR
HOR TEFC 324-6TC CP DIVII CLII
12LYT118

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1