

ABB BALDOR RELIANCE III

Customer information packet

CSPM4310TS

60HP, 3555RPM, 3PH, 60HZ, 364TSC, A36056M, TEF

Class - CLI GP A,B,C,D; CLII GP F,G

Division - Division II

Specifications

Enclosure	TEFC
Frame	364TSC
Frame Material	Cast Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D; CLII GP F,G
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	60.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV CURUSEEV NEMA_PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	131.000 A @ 230.0 V 145.000 A @ 208.0 V 65.400 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.5 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	65.4 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	G

Part Detail

Revision	A
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG0224
Layout	617438-610
Eff. date	05-28-2025
CD Diagram	416820-002
Poles	02
Leads	3#4,6#6
Proprietary	False
Created date	12-10-2024

Lifting Lugs	Standard Lifting Lugs
Max Speed	4200 rpm
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A36056M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	31.36 IN
Power Factor	91
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3555 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP2496L	
MOBILE POLYREX EM	

NP4562L

CAT NO	CSPM4310TS		SPEC NO.		A36-0004-0224			I.P.		55					
HP	60	AMPS	131/65.4		VOLTS	230/460		DESIGN	B						
FRAME SIZE	364TSC	RPM	3555		MAX RPM	4200	HZ	60	AMB	40	C				
D.E. BRG.	65BC03J30X		PH.3	3	DUTY	CONT		INSUL.CLASS		F					
O.D.E. BRG.	65BC03J30X		TYPE P		P	ENCL	TEFC	SF	1.15	CODE	G				
POWER FACTOR	91	MAX CORR KVAR		5		NEMA NOM EFFICIENCY				94.5		MOTOR WEIGHT		LBS	
CL.I,DIV 2,GRP:	A,B,C,D	T.CODE	T3		CL.1,ZONE 2,GRP:				IIA,IIB,IIC		T=	200	C	INVERTER T.CODE	T3
CL.II,DIV 2,GRP:	F,G	T.CODE	T3C		CL II ZONE 22 GRPS IIIB				T=		160	C	INVERTER T.CODE		T3
ID LOGO	INV TYPE:	VPWM	CT	15	TO	60	VT	3	TO	60	CHP	60	TO	70	
ID LOGO	1.0 SF VPWM		WK2		LBFT2	SL HZ		0.75		MAG CUR		28.2/14.1			
SER.NO.			MEETS INTENT OF IEEE-45						FOR WEATHER PROTECTION						

ABB BALDOR RELIANCE III							CUSTOMER INFORMATION PACKET							CSPM4310TS - 60HP, 3555RPM, 3PH, 60HZ, 364TSC, A36056M, TEF						
S/O			FRAME			HP			TYPE			PHASE/ HERTZ			RPM			VOLTS		
			364			60			P			3/60			3555			230/460		
AMPS			DUTY			AMB °C/ INSUL			S.F.			NEMA DESIGN			CODE LETTER			ENCLOSURE		
131/65.4			CONT			40/F			1.15			B			G			TEFC		
E/S			ROTOR			TEST S.O.			TEST DATE			STATOR RES. @25 °C OHMS (BETWEEN LINES)								
491281			418141005XE			---			---			.0254/.101								
PERFORMANCE																				
LOAD			HP			AMPERES			RPM			% POWER FACTOR			% EFFICIENCY					
NO LOAD			0			14.1			3600			7.60			0					
1/4			15.0			20.9			3589			73.2			92.1					
2/4			30.0			33.6			3579			88.4			94.7					
3/4			45.0			48.8			3567			90.8			95.0					
4/4			60.0			65.4			3555			90.7			94.6					
5/4			75.0			82.7			3542			90.4			94.0					
SPEED TORQUE																				
						RPM			TORQUE % FULL LOAD			TORQUE LB.-FT.			AMPERES					
LOCKED ROTOR						0			205			182			431					
PULL UP						1565			178			157			352					
BREAKDOWN						3386			232			205			212					
FULL LOAD						3555			100			88.6			65.4					
AMPERES SHOWN FOR 460 VOLT CONNECTION. IF OTHER CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.																				
TYPICAL DATA XE MOTOR-NEMA NOM. EFF. 94.5 % GUARANTEED MIN. EFF. 93.6%																				
						DRAWN BY: <u>W. L. SMITH</u> CHECKED BY: <u>G. R. WEBB</u> APPROVED BY: <u>E.J. CHRISTIAN</u> DATE: <u>03/11/02</u>						AC MOTOR PERFORMANCE DATA			A36WG0224-R004 DATE ISSUED 01/11/22					

FRAME 364

VOLTS 230/460

NEMA DESIGN B

TEST S.O. TYPICAL DATA

HP 60

AMPS 131/65.4

CODE LETTER G

TEST DATE ---

TYPE P

DUTY CONT

ENCLOSURE TEFC


STATOR RES. @ 25°C .0254/.101

PHASE / HERTZ 3/60

AMB °C / INSUL 40/F

E/S 491281

OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 230/460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.



DRAWN BY: W. L. SMITH
CHECKED BY: G. R. WEBB
APPROVED BY: E.J. CHRISTIAN
DATE: 03/11/02

AC MOTOR
PERFORMANCE
DATA

A36WG0224-R004

ISSUE DATE 01/11/22

FRAME 364

RPM 3555

S.F. 1.15

ROTOR 418141005XE

HP 60

VOLTS 230/460

NEMA DESIGN B

TEST S.O. TYPICAL DATA

TYPE P

AMPS 131/65.4

CODE LETTER G

TEST DATE ---

PHASE / HERTZ 3/60

DUTY CONT


ENCLOSURE TEFC

STATOR RES. @ 25°C .0254/.101

AMB °C / INSUL 40/F

E/S 491281

OHMS (BETWEEN LINES)



MOTOR INITIAL TEMPERATURE:

132° C FOR OVERLOAD AND ACC.

132° C FOR LOCKED-ROTOR

**THERMAL LIMIT CURVE
XE MOTOR-NEMA NOM. EFF. 94.5 %**

AMPERES SHOWN FOR 230/460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.




**DRAWN BY: W. L. SMITH
CHECKED BY: G. R. WEBB
APPROVED BY: E.J.CHRISTIAN
DATE: 03/11/02**

**AC MOTOR
PERFORMANCE
DATA**



A36WG0224-R004

ISSUE DATE 01/11/22



416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED



(N.P. 1575-B)

REV. DESC: FONT CHANGE FOR PDF SEARCHABLE		
REV. LTR: A	VERSION: 01	TDR: 000001009382
FILE: \MGA\00000\661	REVISED: 02:46:19 02/13/2020	BY: MGHMTT
MTL: —		

BALDOR - RELIANCE®

CONN DIAG — STANDARD 9 LEAD, DELTA-CONNECTED
SH 1 of 1

416820-002