

ABB BALDOR RELIANCE III

Customer information packet

CSSWDM3538

.5HP, 1775RPM, 3PH, 60HZ, 56C, 3514M, TENV, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TENV
Frame	56C
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ 208.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.020 A @ 230.0 V 1.900 A @ 208.0 V 1.010 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	81.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	B
Type	AC
Mech. spec.	35V814
Base	
Status	PRD/A
Elec. spec.	35WGG069
Layout	35LYV814
Eff. date	07-22-2024
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	09-15-2023

High Voltage Full Load Amps	1.0 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Finish	UNPAINTED
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3514M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	11.09 IN
Power Factor	63
Product Family	Wash Down All Stainless Steel
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1951A01												
CAT.NO.	CSSWDM3538											
SPEC.	35V814G069G2											
HP	.5											
VOLTS	208-230/460											
AMP	1.9-2.02/1.01											
RPM	1775											
FRAME	56C			HZ		60		PH		3		
SER.F.	1.25	CODE		N	DES		B	CLASS		F		
NEMA-NOM-EFF	81.5			PF		63						
RATING	40C AMB-CONT											
CC												
DE	6205			ODE		6203						
ENCL	TENV	SN										
	SFA 2.16-2.2/1.1											
	20:1CT 20:1VT											

AC Induction Motor Performance Data

Record # 101696

Typical performance - not guaranteed values

Winding: 35WGG069-R088			Type: 3514M		Enclosure: TENV		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		.5	Full Load Torque		1.48 LB-FT		
Volts		208-230/460	Start Configuration		direct on line		
Full Load Amps		1.9-2.02/1.01	Breakdown Torque		8 LB-FT		
R.P.M.		1775	Pull-up Torque		4.4 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		5.1 LB-FT	
NEMA Design Code		B	KVA Code		N		
Service Factor (S.F.)		1.25	Starting Current		8.4 A		
NEMA Nom. Eff.		81.5	Power Factor		63		
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		19°C
S.F. Amps		2.16-2.2/1.1	Temp. Rise @ S.F. Load		21°C		
			Locked-rotor Power Factor		66.8		
			Rotor inertia		0.101 lb-ft²		

Load Characteristics 460 V, 60 Hz, 0.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	24	37	48	58	65	71	65
Efficiency	58.9	72.5	78.4	80.5	81.6	81.5	81.6
Speed	1793	1788	1782	1776	1771	1763	1771
Line amperes	0.85	0.89	0.94	1.01	1.11	1.21	1.11

ABB Motors and Mechanical Inc.

WINDING # 35WGG069

Typical performance - not guaranteed values.

0.5 HP 3 PH 60 HZ 1775 RPM 460 V 3514M

TORQUES (LB-FT) : PO=8 PU=4.4 LR=5.1 LRA=8.4





