

ABB BALDOR RELIANCE III

Customer information packet

CTM3768T

5 AIR OVERHP, 1145RPM, 3PH, 60HZ, 215T, 0736M

Class - None

Division - Not Applicable

Specifications

Enclosure	TEAO
Frame	215T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ 230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	7.700 A @ 460.0 V 15.900 A @ 208.0 V 15.400 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	87.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	C
Type	AC
Mech. spec.	07N391
Base	
Status	PRD/A
Elec. spec.	07WGT573
Layout	07LYN391
Eff. date	06-06-2024
CD Diagram	CD0005
Poles	06
Leads	9#14
Proprietary	False
Created date	03-17-2023

High Voltage Full Load Amps	7.7 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0736M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	19.54 IN
Power Factor	69
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1145 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1258									
CAT.NO.	CTM3768T								
SPEC.	07N391T573H1								
HP	5 AIR OVER								
VOLTS	208-230/460								
AMP	15.9-15.4/7.7								
RPM	1145								
FRAME	215T	HZ	60		PH	3			
SER.F.	1.15	CODE	K	DES	A	CL	F		
NEMA-NOM-EFF	87.5	PF	69						
RATING	40C AMB-CONT								
CC									
DE	6307	ODE	6206						
ENCL	TEAO	SN							
	1275 FPM 170 CFM								

AC Induction Motor Performance Data

Record # 99016

Typical performance - not guaranteed values

Winding: 07WGT573-R001			Type: 0736M		Enclosure: TEAO		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		5 AIR OVER	Full Load Torque		22.71 LB-FT		
Volts		208-230/460	Start Configuration		direct on line		
Full Load Amps		15.9-15.4/7.7	Breakdown Torque		76 LB-FT		
R.P.M.		1145	Pull-up Torque		52.9 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		59.6 LB-FT	
NEMA Design Code		A	KVA Code	K	Starting Current		51.5 A
Service Factor (S.F.)		1.15		No-load Current		4.21 A	
NEMA Nom. Eff.		87.5	Power Factor	69	Line-line Res. @ 25°C		1.87 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		58°C	
S.F. Amps				Temp. Rise @ S.F. Load		70°C	
				Locked-rotor Power Factor		23.8	
				Rotor inertia		0.895 lb-ft²	

Load Characteristics 460 V, 60 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	32	51	63	69	74	76	72
Efficiency	81.9	87.1	88.9	87.5	86.4	84.1	86.8
Speed	1189	1179	1168	1156	1143	1126	1148
Line amperes	4.49	5.23	6.28	7.72	9.21	11	8.61


ABB Motors and Mechanical Inc.

WINDING # 07WGT573

Typical performance - not guaranteed values.

5 HP 3 PH 60 HZ 1145 RPM 460 V 0736M

TORQUES (LB-FT): PO=76 PU=52.9 LR=59.6 LRA=51.5



AC Induction Motor Performance Data

Record # 99017

Typical performance - not guaranteed values

Winding: 07WGT573-R001			Type: 0736M		Enclosure: TEAO		
Nameplate Data			208 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		5 AIR OVER	Full Load Torque		22.88 LB-FT		
Volts		208-230/460	Start Configuration		direct on line		
Full Load Amps		15.9-15.4/7.7	Breakdown Torque		60.8 LB-FT		
R.P.M.		1145	Pull-up Torque		40.8 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		46 LB-FT	
NEMA Design Code		A	KVA Code	K	Starting Current		90 A
Service Factor (S.F.)		1.15		No-load Current		6.81 A	
NEMA Nom. Eff.		87.5	Power Factor	69	Line-line Res. @ 25°C		0.466 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		60°C	
S.F. Amps				Temp. Rise @ S.F. Load		76°C	
				Locked-rotor Power Factor		23.8	
				Rotor inertia		0.895 lb-ft²	

Load Characteristics 208 V, 60 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	41	61	71	75	77	76	76
Efficiency	85.5	88.9	89.7	87.5	85.6	81.8	86.4
Speed	1187	1175	1162	1147	1129	1101	1136
Line amperes	7.59	9.53	12.24	15.85	19.82	25.18	18.2


ABB Motors and Mechanical Inc.


WINDING # 07WGT573

Typical performance - not guaranteed values.


5 HP 3 PH 60 HZ 1145 RPM 208 V 0736M

TORQUES (LB-FT): PO=60.8 PU=40.8 LR=46 LRA=90





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005